

HEYCO



Heyco® Thick Panel Snap Bushings

Mounting Hole Diameter Range: .375" (9,5 mm) to 2.0" (50,8 mm)

MOUNTING HOLE DIAMETER		PART NO.		DESCRIPTION	PART DIMENSIONS					
in.	mm.	Black	White		A Inside Diameter		B Head Diameter		C Overall Height	
					in.	mm.	in.	mm.	in.	mm.

Single Locking Step for Panel Thickness up to .170" (4,3 mm)

.375	9,5	2017	2018	SB 375-281	.281	7,1	.468	11,9	.406	10,3
1.000	25,4	3085	3088	SBT 1000-790*	.790	20,1	1.130	28,8	.450	11,4

Multiple Locking Steps for Panel Thickness up to .250" (6,4 mm)


.500	12,7	3126	3127	SBT 500-6	.391	9,9	.578	14,7	.562	14,3
.625	15,9	2830	2831	SB 625-500**	.500	12,7	.703	17,9	.531	13,5
.750	19,1	2840	2841	SB 750-625**	.625	15,9	.828	21,0		
.875	22,2	3104	3105	SBT 875-11	.687	17,5	.953	24,2		
1.000	25,4	3108	3109	SBT 1000-12	.766	19,4	1.125	28,6		
1.093-1.125	27,8-28,6	3128	3129	SBT 1093-15	.937	23,8	1.218	30,9		
1.187	30,2	3130	3131	SBT 1187-15	.937	23,8	1.312	33,3	.562	14,3
1.250	31,8	3132	3133	SBT 1250-16	1.000	25,4	1.310	33,2		
1.375	34,9	3110	3111	SBT 1375-16	1.000	25,4	1.500	38,1		
1.500	38,1	3112	3113	SBT 1500-21	1.312	33,3	1.620	41,2		
1.750	44,5	3114	3115	SBT 1750-22	1.375	34,9	1.875	47,6		
2.000	50,8	3116	3117	SBT 2000-26	1.625	41,3	2.125	54,0		

Standard colors black and white. Consult Heyco for other colors.

*Notched head, triple locking finger design.

**Single Locking Step for Panel Thickness up to .250" (6,4 mm).

- For use in mounting panels up to 1/4" thick.
- Convert raw-edged holes to smooth, neat, insulated holes.
- Insulate and mechanically protect electrical and telecommunications cables, tubing, hose, rope, and utility lines.
- Locking fingers snap into holes with fingertip pressure.
- Locking fingers in fractional increments up to the maximum panel thickness.
- Withstand a push back force of >35 pounds.
- Available in multiple sizes for use in .375" (9,5 mm) to 2.0" (50,8 mm) diameter holes.



Heyco® Knock Out Snap Bushings

BOX HOLE DIAMETER		TRADE SIZE	PART NO. Black	DESCRIPTION	PART DIMENSIONS					
in.	mm.				A Inside Diameter		B Head Diameter		C Overall Height	
					in.	mm.	in.	mm.	in.	mm.

Multiple Locking Steps for Box Thickness up to .125" (3,2 mm)

.875	22,2	1/2	2126	SB 875-11	.687	17,5	.953	24,2	.453	11,5
1.093-1.125	27,8-28,6	3/4	2166	SB 1093-15	.937	23,8	1.218	30,9		
1.375	34,9	1	2210	SB 1375-16	1.014	25,8	1.490	37,3		
1.750	44,5	1-1/4	2300	SB 1750-22	1.375	34,9	1.875	47,6		
2.000	50,8	1-1/2	2406	SB 2000-28	1.750	44,5	2.125	54,0		

Multiple Locking Steps for Box Thickness up to .250" (6,4 mm)

2.500	63,5	2	2420	SB 2.500-31	1.970	50,0	2.660	67,5	.720	8,3
-------	------	---	------	-------------	-------	------	-------	------	------	-----

Standard color black. Consult Heyco for white and other colors. For thicker boxes, see below.

- For use in boxes and enclosures up to thicknesses shown.

Material	Nylon 6/6
Certifications	Recognized under the Component Program of Underwriters' Laboratories, File E15331 Certified by Canadian Standards Association, File 8919
Flammability Rating	94V-2
Material Temperature Index	257°F (125°C)–Maximum temperature on part not to exceed 221°F (105°C)

Quick Specs