




Compact Size
Panel Mount Indicator, Non-Relampable
LED Technology
Mounting Hole, Ø 0.310"



All dimensions are in inches



Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard
 Due to compact size, components (resistors, diodes)
 will be installed in the leads.

Storage temperature T_{STG} : -25°C - +80°C
 Ambient temperature T_A : -20°C - +60°C
 Voltage tolerance V_{OP} : ±10%

Part No.	Lens Color	Voltage (DC)	Current (mA)	Rated Life
LED 6V Series				
WL-2191SL1-6V	Red	5V-6V	20mA	100,000 Hrs
WL-2191SL5-6V	Green	5V-6V	20mA	100,000 Hrs
WL-2191SL6-6V	Blue	5V-6V	20mA	100,000 Hrs
WL-2191SL7-6V	Yellow	5V-6V	20mA	100,000 Hrs
LED 12V Series				
WL-2191SL1-12V	Red	12V-14V	20mA	100,000 Hrs
WL-2191SL5-12V	Green	12V-14V	20mA	100,000 Hrs
WL-2191SL6-12V	Blue	12V-14V	20mA	100,000 Hrs
WL-2191SL7-12V	Yellow	12V-14V	20mA	100,000 Hrs
LED 24V Series				
WL-2191SL1-24V	Red	24V-28V	20mA	100,000 Hrs
WL-2191SL5-24V	Green	24V-28V	20mA	100,000 Hrs
WL-2191SL6-24V	Blue	24V-28V	20mA	100,000 Hrs
WL-2191SL7-24V	Yellow	24V-28V	20mA	100,000 Hrs

Body Material: Nylon, white
 Lens Material: Polycarbonate
 Bezel Material: Chrome
 Wire Gauge: 18 AWG
 Wire Strip: 1/2"
 Anode(+): Red lead
 Notes: Tinnerman clips available separately.

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.
 Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	04/04/12	Compact Size Panel Mount Indicators LED	Datasheet: WL-2191SLX-XXX Series	Rev: 1
Checked	EB	04/04/12			
Approved	EB	04/05/12			