



NO MERCURY ADDED


Description	: Mercury Free Extra Heavy Duty Battery, AA Size
Chemical System	: Zinc Chloride
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: Ø13.9 mm x 50.0 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Metal jacket with PVC tube insulation
Applications	: All electronic devices, e.g. toys, photographic equipment, data banks, calculators, audio appliances, remote controls, paging machines.
Warranty Period	: 36 months
Average Weight	: 18g

Cross References:



GP	JIS	IEC	Eveready
15G	R6P	R6	1215

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
10 Ohms	24 Hrs/ Day	0.9V	335 Mins



Model No.: **GP15G**



Unit : mm