



Product: [2413](#) 

Category 6+ Enhanced Cable, 4 Pair, U/UTP, CMP

Product Description

Category 6+ Enhanced Premise Horizontal Cable (350MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Construction Details

Conductor

AWG	Stranding	Material	Number of Pairs
23	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown
Bonded-Pair:	No

Outer Jacket Material

Separator Material	Material	Material Trade Name	Nom. Diameter	Ripcord
Dielectric Tape (Patented)	PVC - Polyvinyl Chloride	Flamarrest®	0.224 in	Yes

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. DCR Unbalance	Max. Capacitance Unbalance	Nom. Mutual Capacitance
78 Ohm/km	3%	330 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew
100 MHz	537.6 ns/100m	35 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	79.3 dB	77.3 dB	77.3 dB	75.3 dB	70.8 dB	67.8 dB	20.0 dB	100 ± 15	102 ± 15
4 MHz	3.7 dB/100m	70.3 dB	68.3 dB	66.5 dB	64.5 dB	58.8 dB	55.8 dB	23.6 dB	100 ± 15	100 ± 15
8 MHz	5.3 dB/100m	65.8 dB	63.8 dB	60.5 dB	58.5 dB	52.7 dB	49.7 dB	25.3 dB	100 ± 15	100 ± 15
10 MHz	5.9 dB/100m	64.3 dB	62.3 dB	58.4 dB	56.4 dB	50.8 dB	47.8 dB	26.0 dB	100 ± 15	100 ± 15
16 MHz	7.4 dB/100m	61.2 dB	59.2 dB	53.8 dB	51.8 dB	46.7 dB	43.7 dB	26.0 dB	100 ± 15	100 ± 15
20 MHz	8.3 dB/100m	59.8 dB	57.8 dB	51.4 dB	49.4 dB	44.8 dB	41.8 dB	26.0 dB	100 ± 15	100 ± 15
25 MHz	9.4 dB/100m	58.3 dB	56.3 dB	49.0 dB	47.0 dB	42.8 dB	39.8 dB	25.5 dB	100 ± 15	100 ± 15
31.25 MHz	10.5 dB/100m	56.9 dB	54.9 dB	46.4 dB	44.4 dB	40.9 dB	37.9 dB	25.0 dB	100 ± 15	100 ± 15
62.5 MHz	15.1 dB/100m	52.4 dB	50.4 dB	37.3 dB	35.3 dB	34.9 dB	31.9 dB	23.5 dB	100 ± 15	100 ± 15

100 MHz	19.3 dB/100m	49.3 dB	47.3 dB	30.0 dB	28.0 dB	30.8 dB	27.8 dB	22.5 dB	100 ± 15	100 ± 15
155 MHz	24.5 dB/100m	46.4 dB	44.4 dB	21.9 dB	19.9 dB	27.0 dB	24.0 dB	21.6 dB	100 ± 22	100 ± 15
200 MHz	28.2 dB/100m	44.8 dB	42.8 dB	16.6 dB	14.6 dB	24.8 dB	21.8 dB	21.0 dB	100 ± 22	100 ± 15
250 MHz	31.8 dB/100m	43.3 dB	41.3 dB	11.5 dB	9.5 dB	22.8 dB	19.8 dB	20.5 dB	100 ± 32	100 ± 15
300 MHz	35.2 dB/100m	42.1 dB	40.1 dB	6.9 dB	4.9 dB	21.3 dB	18.3 dB	20.1 dB	100 ± 32	100 ± 15
350 MHz	38.4 dB/100m	41.1 dB	39.1 dB	2.7 dB	0.7 dB	19.9 dB	16.9 dB	19.8 dB	100 ± 32	100 ± 15
400 MHz	41.5 dB/100m	40.3 dB	38.3 dB			18.8 dB	15.8 dB	19.5 dB	100 ± 32	100 ± 15
450 MHz	44.3 dB/100m	39.5 dB	37.5 dB			17.7 dB	14.7 dB	19.2 dB	100 ± 32	100 ± 15
500 MHz	47.1 dB/100m	38.8 dB	36.8 dB			16.8 dB	13.8 dB	19.0 dB	100 ± 32	100 ± 15
550 MHz	49.7 dB/100m	38.2 dB	36.2 dB			16.0 dB	13.0 dB	18.8 dB	100 ± 32	100 ± 15

Voltage

UL Voltage Rating
300 V (CMP), 300 V (CL3P)

Mechanical Characteristics

Temperature

UL Rating	Operating	Installation	Storage
90°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in	2.25 in

Max. Pull Tension:	25 lbs
Bulk Cable Weight:	26 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, FT6, IEC 60332-1-2
NEC / UL Compliance:	800, CMP;CMP-LP (0.5A);CL3P-LP (0.5A)
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732-2013
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Part Number

Non-Plenum Number:	2412
--------------------	------

Variants

Item #	Color	Putup Type	Length	UPC
2413 0101000	Black	Reel	1,000 ft	612825061762
2413 010A1000	Black	Reel-in-Box	1,000 ft	612825061755
2413 010U1000	Black	UnReel	1,000 ft	612825131502
2413 0102500	Black	Reel	2,500 ft	612825061748
2413 D151000	Blue	Reel	1,000 ft	612825061601
2413 D15A1000	Blue	Reel-in-Box	1,000 ft	612825061618
2413 D15U1000	Blue	UnReel	1,000 ft	612825061793
2413 D152500	Blue	Reel	2,500 ft	612825061625
2413 0081000	Gray	Reel	1,000 ft	612825061717
2413 008A1000	Gray	Reel-in-Box	1,000 ft	612825061724
2413 008U1000	Gray	UnReel	1,000 ft	612825061809
2413 0051000	Green	Reel	1,000 ft	612825061663

2413 005A1000	Green	Reel-in-Box	1,000 ft	612825061687
2413 005U1000	Green	UnReel	1,000 ft	612825062226
2413 0052500	Green	Reel	2,500 ft	612825061670
2413 0035000	Orange			612825381068
2413 0035000	Orange			612825381068
2413 0031000	Orange	Reel	1,000 ft	612825061694
2413 003A1000	Orange	Reel-in-Box	1,000 ft	612825061700
2413 003U1000	Orange	UnReel	1,000 ft	612825062202
2413 012A1000	Pink	Reel-in-Box	1,000 ft	612825061786
2413 007A1000	Purple	Reel-in-Box	1,000 ft	612825061779
2413 002A1000	Red	Reel-in-Box	1,000 ft	612825061731
2413 0091000	White	Reel	1,000 ft	612825061571
2413 009A1000	White	Reel-in-Box	1,000 ft	612825061588
2413 009U1000	White	UnReel	1,000 ft	612825061816
2413 0092500	White	Reel	2,500 ft	612825061595
2413 0041000	Yellow	Reel	1,000 ft	612825061632
2413 004A1000	Yellow	Reel-in-Box	1,000 ft	612825061649
2413 004U1000	Yellow	UnReel	1,000 ft	612825062219
2413 0042500	Yellow	Reel	2,500 ft	612825061656

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.412 Revision Date: 07-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[2413 008U1000](#) [2413 009U1000](#) [2413 D15U1000](#) [2413 D15A1000](#) [2413 D151000](#) [2413 D152500](#) [2413 002A1000](#)
[2413 003A1000](#) [2413 0031000](#) [2413 004A1000](#) [2413 0041000](#) [2413 0042500](#) [2413 005A1000](#) [2413 0051000](#)
[2413 0052500](#) [2413 007A1000](#) [2413 008A1000](#) [2413 0081000](#) [2413 009A1000](#) [2413 0091000](#) [2413 0092500](#) [2413](#)
[010A1000](#) [2413 0101000](#) [2413 0102500](#) [2413 012A1000](#)