



# **DK Cable junction boxes** **cable entry via elastic membranes and integrated M 20 thread**

- rated insulation voltage: 400 V
- degree of protection: IP 55
- degree of protection: IP 65 (ADM)
- material: thermoplastic
- colour: grey, RAL 7035




|                |                                                                                                                            |                                                                                     |
|----------------|----------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>DN 2000</b> | <p>cable entry: 8 membranes, closed<br/> (sealing range: Ø 3-12 mm)<br/> integrated M 20 thread<br/> without terminals</p> |  |
|----------------|----------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|



|                |                                                                                                                                                                                       |                                                                                     |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>DN 2030</b> | <p>included cable entry 3 ADM 20,<br/> (sealing range: Ø 6.5-13.5 mm)<br/> 8 membranes, closed<br/> (sealing range: Ø 3-12 mm)<br/> integrated M 20 thread<br/> without terminals</p> |  |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|



|                |                                                                                                                                                                                                                                                                                 |                                                                                     |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>DN 2035</b> | <p>5-pole,<br/> per pole 6 x 1.5 mm<sup>2</sup> sol, 4 x 2.5 mm<sup>2</sup> sol,<br/> 3 x 4 mm<sup>2</sup> sol<br/> included cable entry 3 ADM 20,<br/> (sealing range: Ø 6.5-13.5 mm)<br/> 8 membranes, closed<br/> (sealing range: Ø 3-12 mm)<br/> integrated M 20 thread</p> |  |
|----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|



|                                                                                                                            |                                   |                                         |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------------|-----------------------------------------|
| <p><b>Cable gland</b><br/> <b>degree of protection: IP 65</b><br/> colour: grey, RAL 7035<br/> material: thermoplastic</p> |                                   |                                         |
| <b>ADM 20</b>                                                                                                              | <p>ISO thread<br/> M 20 x 1.5</p> | <p>sealing range<br/> Ø 6.5-13.5 mm</p> |