


SOT23 NPN SILICON PLANAR RF TRANSISTORS

ISSUE 4 – MARCH 2001

PARTMARKING DETAILS — BFS17L - E1L
BFS17H - E1H

BFS17L
BFS17H



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	25	V
Collector-Emitter Voltage	V_{CEO}	15	V
Emitter-Base Voltage	V_{EBO}	2.5	V
Peak Pulse Current	I_{CM}	50	mA
Continuous Collector Current	I_C	25	mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	330	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Collector Cut-Off Current	I_{CBO}			10 10	nA μA	$V_{CB}=10V, I_E=0$ $V_{CB}=10V, I_E=0,$ $T_{amb} = 100^{\circ}C$
Static Forward Current Transfer Ratio	h_{FE}					
BFS17L		25		100		$I_C=2.0mA, V_{CE}=1.0V$
BFS17H		70		200		$I_C=2.0mA, V_{CE}=1.0V$
		20		125		$I_C=25mA, V_{CE}=1.0V$
Transition Frequency	f_T		1.0 1.3		GHz GHz	$I_C=2.0mA, V_{CE}=5.0V$ $f=500MHz$ $I_C=25mA, V_{CE}=5.0V$ $f=500MHz$
Feedback Capacitance	$-C_{re}$		0.85		pF	$I_C=2.0mA, V_{CE}=5V, f=1MHz$
Output Capacitance	C_{obo}			1.5	pF	$V_{CB}=10V, f=1MHz$
Input Capacitance	C_{ibo}			2.0	pF	$V_{EB}=0.5V, f=1MHz$
Noise Figure	N		4.5		dB	$I_C=2.0mA, V_{CE}=5.0V$ $R_S=50\Omega, f=500MHz$
Intermodulation Distortion	d_{im}		-45		dB	$I_C=10mA, V_{CE}=6.0V$ $R_L=37.5\Omega, T_{amb}=25^{\circ}C$ $V_o=100mV$ at $f_p=183MHz$ $V_o=100mV$ at $f_q=200MHz$ measured at $f_{(2q-p)}=217MHz$

Spice parameter data is available upon request for this device



BFS17L

BFS17H

TYPICAL CHARACTERISTICS

