



SANDVIK BELZER

Finish: chrome-plated and polished.

Material: brass, with plastic handle.

Head Ø 8 mm.

Magnetic pick-up tool

Product code	EAN code 731415+		Pressure force max. g	L mm	
2535F1	1064495	1	500	460	1t0

2535F1



Finish: chrome-plated magnetic head, Ø 8 mm.

Material: BRASS.

For office and fine-mechanics applications.

Magnetic pick-up tool with joint

Product code	EAN code 731415+		Pressure force max. g	L mm	
2535K	1064501	1	400	235	60

2535K



Finish: chrome-plated magnetic head, Ø 13 mm.

Material: BRASS.

Magnetic pick-up tool, telescopic type

Product code	EAN code 731415+		Pressure force max. g	L mm	
2535T	1064525	1	1200	420-700	245

2535T



Finish: chrome-plated. Flexible shaft with steel core.

Material: BRASS.

For gripping very small parts.

Flexible pick-up tool

Product code	EAN code 731415+		Opening max. Ø	L mm	
2509	1064280	1	14	525	10

2509



Finish: with plastic handle, in wooden case.

With illuminated mirror surface.

Telescopic mirror

Product code	EAN code 731415+		Mirror Ø mm	L mm	
A5530	1738433	1	60	350-800	840

A5530

