

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15266-0774](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 0.50mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 9 Circuits, 0.127m Cable Length, 0.27mm Cable Thickness, Tin (Sn) Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-15266-001 \(PDF\)](#)
[Packaging Specification PK-15266-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable
Series [15266](#)
Comments Contacts on opposite sides, Type D
Crimp Quality Equipment Yes
Overview [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Product Name Premo-Flex™ FFC Jumper
UPC 884982435643

Physical
Cable Length 0.127m
Circuits (Loaded) 9
Circuits (maximum) 9
Packaging Type Bag
Pitch - Termination Interface 0.50mm
Temperature Range - Operating -40°C to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 0.5A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-15266-001
Product Specification PS-15266-001
Sales Drawing SD-15266-001



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[15266Series](#)

Use With
Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION