



Fittings for metallic conduits and metallic overbraid

• SCSB-FM Fixed External Thread

Fixed external thread, nickel plated brass.

Features and Benefits

- Two part fitting comprising shell and body with external thread
- Can be secured with a locknut



Helaguard SCSB-FM Fixed External Thread.

Technical Table

Article-No.	Type	Nominal Ø	Thread Size (metric)	Thread Size (PG)	Pack Cont.
166-34600	SCSB12-FM-M16	12	M16	–	10
166-34607	SCSB12-FM-PG9	12	–	PG9	10
166-34601	SCSB16-FM-M16	16	M16	–	10
166-34602	SCSB16-FM-M20	16	M20	–	10
166-34608	SCSB16-FM-PG11	16	–	PG11	10
166-34603	SCSB20-FM-M20	20	M20	–	10
166-34609	SCSB20-FM-PG16	20	–	PG16	10
166-34604	SCSB25-FM-M25	25	M25	–	10
166-34610	SCSB25-FM-PG21	25	–	PG21	10
166-34605	SCSB32-FM-M32	32	M32	–	2
166-34611	SCSB32-FM-PG29	32	–	PG29	2
166-34606	SCSB40-FM-M40	40	M40	–	1
166-34612	SCSB40-FM-PG36	40	–	PG36	1

All dimensions in mm. Subject to technical changes.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C



• SCSB-SM Swivel External Thread

Swivel external thread, nickel plated brass.

Features and Benefits

- Two part fitting comprising shell and body
- External thread swivels about the main body
- Can be secured with a locknut



Helaguard SCSB-SM Swivel External Thread.

Technical Table

Article-No.	Type	Nominal Ø	Thread Size (metric)	Thread Size (PG)	Pack Cont.
166-34700	SCSB12-SM-M16	12	M16	–	10
166-34707	SCSB12-SM-PG9	12	–	PG9	10
166-34701	SCSB16-SM-M16	16	M16	–	10
166-34702	SCSB16-SM-M20	16	M20	–	10
166-34708	SCSB16-SM-PG11	16	–	PG11	10
166-34703	SCSB20-SM-M20	20	M20	–	10
166-34709	SCSB20-SM-PG16	20	–	PG16	10
166-34704	SCSB25-SM-M25	25	M25	–	10
166-34710	SCSB25-SM-PG21	25	–	PG21	10
166-34705	SCSB32-SM-M32	32	M32	–	2
166-34711	SCSB32-SM-PG29	32	–	PG29	2
166-34706	SCSB40-SM-M40	40	M40	–	1
166-34712	SCSB40-SM-PG36	40	–	PG36	1

All dimensions in mm. Subject to technical changes.