

**SCHROFF**

Project - 0 item(s)

MY PROJECT LIST

PRODUCTS

APPLICATIONS

INDUSTRIES

NEW PRODUCTS

CONFIGURATORS

Products ▾

Search



Home > Front panel (3 U 16 HP), U profile, EMC shielding textile gasket, for IEL/IET/Trapeziform Type 2 handle


**SCHROFF**

Front panel (3 U 16 HP), U profile, EMC shielding textile gasket, for IEL/IET/Trapeziform Type 2 handle



Illustration shows front panel 3 U, 4 HP

Other Views

**Catalog Number: 20848-232**[Back To Product](#)

- For IEL/IET/Trapeziform Type 2 handle
- Stainless steel alignment pin pressed-in
- U profile, shieldable with textile EMC gasket
- Al extrusion, 2.5 mm, front anodized, rear conductive
- Manufacturing process causes various surface structures to appear between 4 to 12 HP and 14 to 16 HP
- Front panel, 3 U, for front mounting

Product family:

Plug-in units

Note:

Please order EMC profile seal separately

Specification:

- IEEE 1101.10
- IEC 60297-3-102
- IEC 60297-3-103
- IEEE 1101.1/11

Material and Surface Finish:

Al, Front Anodized, Rear Passivated

Handle:

- IET
- Trapezoid, Type 2
- IEL

Assembly:

Screw on - Front Side

EMC Shielding:

Shieldable (Textile Gasket)

Type:

Individual Components

Individual Component Type:

Front Panels

Standard pack quantity (SPQ):

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

Select product specifications before modifying or adding to project list or requesting a quote.

Width-HP-defining

16 ▾

[Clear Selection](#)Quantity [Modify Product](#) ▶[Add Item to Project List](#) +**Documents**

Main Catalog - Plug-in units

Links

Native CAD files

Technical Data**Qty** 1 piece (SPQ 5)**Delivery is exclusively made in Standard Pack**

5








FRONT PANEL
FAST TRACK


Quantity (SPQ)	
Width b mm	80.94
For case height [U]	128.4
Thickness mm	2.5
Height U	3
Width HP	16

Delivery Comprises:

Item	Quantity	Description
1	1	U profile, Al, front anodised, side raw, rear colourless chromated
3	1	Alignment pin pressed in, St, alignment via perforated strip

Accessories


	Inserter/extractor handle, type IEL, black, bottom (Rear I/O 6 U top), PU 10 pcs	20817-612	Add Item to Project List +
	Inserter/extractor handle, type IEL, grey, bottom (Rear I/O 6 U top), PU 10 pcs	20817-620	Add Item to Project List +
	Inserter/extractor handle, type IEL, black, bottom (Rear I/O 6 U top), PU 100 pcs	20817-613	Add Item to Project List +
	Inserter/extractor handle, type IEL, grey, bottom (Rear I/O 6 U top), PU 100 pcs	20817-621	Add Item to Project List +
	Inserter/extractor handle, type IET, black, bottom (Rear I/O 6 U top), PU 10 pcs	20817-652	Add Item to Project List +
	Inserter/extractor handle, type IET, grey, bottom (Rear I/O 6 U top), PU 10 pcs	20817-660	Add Item to Project List +
	Inserter/extractor handle, type IET, black, bottom (Rear I/O 6 U top), PU 100 pcs	20817-653	Add Item to Project List +
	Inserter/extractor handle, type IET, grey, bottom (Rear I/O 6 U top), PU 100 pcs	20817-661	Add Item to Project List +
	Microswitch for IEL/IET handle, PU 10 pcs	20817-606	Add Item to Project List +



Label strips for IEL/IET handle, white, sheet with 210pcs (19x9,5), PU 1 pcs

60817-340


[Add Item to Project List](#) +



Label strips for IEL handle, white, sheet with 320pcs (19x4,8), PU 1 pcs

60817-341


[Add Item to Project List](#) +



Board support, die-cast zinc (2xM2.5), 1pcs (SPQ10)

60807-181


[Add Item to Project List](#) +



Panhead screw, cross recess (M2.5x6), steel nickel plated, PU 100 pcs

21101-219

[Add Item to Project List](#) +



Panhead screw, Torx (M2.5x6), steel zinc plated, PU 100 pcs

24560-159


[Add Item to Project List](#) +



Washer (D2.7 DIN 125), steel nickel plated, PU 100 pcs

21100-721


[Add Item to Project List](#) +



Raised countersunk screw, cross recess (M2.5x8), steel nickel plated, PU 100 pcs

21100-429

[Add Item to Project List](#) +



Raised countersunk screw, Torx (M2.5x8), steel nickel plated, PU 100 pcs

24560-164


[Add Item to Project List](#) +



Collar screw, cross recess/slotted (M2.5x12.3), steel nickel plated, PU 100 pcs

21101-101

[Add Item to Project List](#) +



Sleeve, plastic, grey, PU 100 pcs

21100-464

[Add Item to Project List](#) +



Sleeve, stainless steel, PU 100 pcs

21100-662

[Add Item to Project List](#) +



Extractor handle, trapeziform type 2, black, PU 10 pcs

20817-856






[Add Item to Project List](#) +



Extractor handle, trapeziform type 2, black, with alignment pin, PU 10 pcs

20817-831

[Add Item to Project List](#) +

	Extractor handle, trapeziform type 2, dark grey, PU 10 pcs	20817-854	Add Item to Project List +
	Extractor handle, trapeziform type 2, dark grey, with alignment pin, PU 10 pcs	20817-829	Add Item to Project List +
	Extractor handle, trapeziform type 2, light grey, PU 10 pcs	20817-858	Add Item to Project List +
	Extractor handle, trapeziform type 2, light grey, with alignment pin, PU 10 pcs	20817-833	Add Item to Project List +
	EMC shielding textile gasket, -40...+70°C, 3 U, PU 10 pcs	21101-853	Add Item to Project List +
	EMC shielding textile gasket, -40...+70°C, 3 U, PU 100 pcs	21101-854	Add Item to Project List +
	EMC shielding textile gasket, -40 ... +85 °C, 3U, PU 10 pcs	21102-853	Add Item to Project List +
	EMC shielding textile gasket, -40 ... +85 °C, 3U, PU 100 pcs	21102-854	Add Item to Project List +

EXPLORE

[About Us](#)
[Services & Capabilities](#)
[News & Events](#)
[Newsletter Subscriptions](#)
[Strategic Partnerships](#)
[Investor Relations](#)

CONTACT

[Customer Service](#)
[Find a Sales Office or Distributor](#)
[Global Locations](#)
[Product Compliance & Certifications](#)
[Partner Login](#)

DOWNLOAD

[Download Center](#)
[Reference Projects](#)
[Videos](#)
[Product Configurators](#)
[Warranties and Terms of Sale & Procurement](#)

© 2018 nVent. All rights reserved | [Privacy Policy](#) | [Terms of Use](#) | [Cookie Policy](#) | [Imprint](#) | [Site Map](#)

Connect With Us

