


**Panel Mount Indicator, Non-Relampable
Neon Technology
Mounting Hole, Ø 0.380"**



All dimensions are in inches



Recommended panel thickness: 0.030" to 0.250"

.187 x .020 terminals are standard

Storage temperature	T _{STG} : -25°C - +80°C
Ambient temperature	T _A : -20°C - +60°C
Voltage tolerance	V _{OP} : ±10%

[illegible]

Body Material: Nylon, white
 Lens Material: Polycarbonate
 Bezel Material: Stainless steel
 Terminals: Quick-connect, tinned brass
 Gaskets: Buna-N

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.

Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	03/01/10	Panel Mount Indicators Neon	Datasheet: WL-601XQMX Series	Rev: 1
Checked	EB	03/01/10			
Approved	EB	03/02/10			