

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

,19


© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		REV		ZONE		LTR		REVISIONS		DATE		APPD	
AJ	16	P	F					F		REDWN, REV & ADD 3--9 PER AJ-4560		2-8-91		BAS	



VIEW X

VIEW Y
SAME AS VIEW X
EXCEPT AS SHOWN

- 1 BERYLLIUM COPPER PER QQ-C-530
- 2 GOLD PLATE PER MIL-G-45204
1.27µm [0.00050] MINIMUM THICK
- 3 GOLD PLATE PER MIL-G-45204
0.76µm [0.00030] MINIMUM THICK
- 4 GOLD PLATE PER MIL-G-45204
2.54µm [0.00100] MINIMUM THICK
- 5 SILVER PLATE PER QQ-S-365
2.54µm [0.00100] MINIMUM THICK

Y	4	10.39 [0.409]	5.08 [0.200]	0.79 [0.031]	3-331368-9
Y	5	10.39 [0.409]	5.08 [0.200]	0.79 [0.031]	3-331368-8
X	3	10.39 [0.409]	5.84 [0.230]	0.36 [0.014]	2-331368-4
Y	3	10.39 [0.409]	5.08 [0.200]	0.46 [0.031]	2-331368-3
X	3	10.39 [0.409]	5.08 [0.200]	0.46 [0.018]	2-331368-2
X	3	10.69 [0.421]	5.08 [0.200]	0.89 [0.035]	2-331368-1
X	3	11.73 [0.462]	5.08 [0.200]	0.61 [0.024]	1-331368-6
X	3	10.39 [0.409]	5.08 [0.200]	0.46 [0.018]	1-331368-4
X	3	10.39 [0.409]	5.08 [0.200]	0.61 [0.024]	1-331368-2
Y	3	10.39 [0.409]	5.08 [0.200]	0.79 [0.031]	331368

VIEW	FINISH	C	B	A	PART NUMBER
------	--------	---	---	---	-------------

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm (INCHES)
TOLERANCES ON:
2 PLC DEC ± 0.20 (0.008)
3 PLC DEC ± -
ANGLES ± -

MATERIAL



FINISH

SEE TABLE

DR 2-8-91
B. SCOTTCHK 3-20-91
J. LIPPERTAPPD 4-3-91
M. PHILLIPSAPPD 4-3-91
J. LIPPERT

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

AMPAMP Incorporated
Harrisburg, PA 17105-3608

NAME

CONTACT, RECEPTACLE,
DUAL CRIMP, SERIES BNC

SIZE

C

CAGE CODE

00779

DRAWING NO

331368

SCALE 12:1

SHEET 1 OF 1

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-331368-9](#)