



DESCRIPTION: HIGH DENSITY FEMALE RIGHT ANGLE



POS.	A	B	C	D	E	F
15	1.213	0.984	0.644	0.090	0.311	0.496
	30.80	24.99	16.34	2.29	7.90	12.60
26	1.543	1.312	0.966	0.090	0.311	0.496
	39.19	33.32	24.53	2.29	7.90	12.60
44	2.087	1.852	1.512	0.090	0.311	0.496
	53.00	47.04	38.40	2.29	7.90	12.60
62	2.732	2.500	2.156	0.095	0.311	0.496
	69.30	63.50	54.76	2.41	7.90	12.60

181-XXX-212-XX1

SERIES _____
POSITIONS _____
015
026
044
062
GENDER _____
2 = FEMALE
TERMINATION _____
1 = DIP SOLDER
SHELL PLATING _____
2 = TIN
HARDWARE OPTIONS _____
00 = NO HARDWARE
16 = .1200/INSIDE GRND STRAPS
17 = 4-40 INSERTS/INSIDE GRND STRAPS
18 = 4-40 SCREWLOCKS/INSIDE GRND STRAPS
43 = .1200/METAL SHELL
45 = 4-40 INSERTS/METAL SHELL
48 = 4-40 SCREWLOCKS/METAL SHELL
53 = 4-40 INSERTS/BOARDLOCKS
56 = 4-40 SCREWLOCK/BOARDLOCKS
PLATING OPTIONS _____
1 = GOLD FLASH MATING AREA
TIN/LEAD SOLDER TAILS


ELECTRICALS:
CURRENT RATING: 2 AMPS
CONTACT RESISTANCE: 15 mOHMS MAX.
INSULATOR RESISTANCE: 1000MOHMS MIN.
VOLTAGE: 500V FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C

MATERIALS:
SHELL: STEEL, TIN PLATED
INSULATOR: PBT - BLACK (UL-94-VO)
CONTACT: BRASS, GOLD FLASH MATING AREA,
TIN/LEAD ON SOLDER TAILS


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS		DATE: 9-24-98	
			CHECKED:		DATE:	
	NorComp		SCALE:		SHEET OF	
DWG NO.			REV 6			
		181-XXX-212-XX1				

DESCRIPTION: HIGH DENSITY RIGHT ANGLE FEMALE FOOTPRINT


78 POSITION FEMALE




62 POSITION FEMALE



26 POSITION FEMALE




15 POSITION FEMALE



VIEWS ARE COMPONENT SIDE

44 POSITION FEMALE



	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 10-29-01	
		CHECKED:		DATE:	
			SCALE:	SHEET 1 OF 1	REV 4
			DWG NO. HIGH DENSITY RIGHT ANGLE FEMALE FOOTPRINT		