

HBL5466C -- Insulgrip Series Plug




2P3W, 20A 250V, 6-20P, Black & White Nylon

Product Specifications

Product Type	 Plugs
Body Style	Straight
Standard	NEMA
Amperage	20A
Voltage	250V
Poles and Wires	2 Pole, 3 Wire Grounding
Hospital Grade ?	No
Plug/Connector Grade	Insulgrip
Color	 Black
NEMA No.	6-20P
Horsepower	2
Cord Dia.	.230"-.720" (5.8-18.3)

Description	Straight Blade Plug
Type	2 Pole, 3 Wire, Grounding
Rating	20A, 250V
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280
IP Suitability	IP20
Housing Material	Nylon-Black
Blade Holder Material	Nylon-Natural
Retainer Material	Polycarbonate-Clear
Cord Clamp Material	Nylon-Natural
Contact Blades Material	.060" (1.5) Brass
Ground Contact Blade Material	.040" (1.0) Copper Alloy
Terminal Screw Material	#8-32 Brass /Ni plated for neutral
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Wire Clamps Material	.062" (1.8) Steel-nickel finish
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 HB or better.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing
Catalog Page	Click here for catalog page A26
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-A
UPC Number	78358517470
Weight in LBs	0.15



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031

