

SOT23 NPN SILICON PLANAR


SMALL SIGNAL TRANSISTORS

ISSUE 2 - JUNE 1995

PARTMARKING DETAILS	– BCW31 – D1	BCW31R – D4
	BCW32 – D2	BCW32R – D5
	BCW33 – D3	BCW33R – D6

COMPLEMENTARY TYPES	– BCW31 - BCW29
	– BCW32 - BCW30
	– BCW33 - N/A

BCW31
BCW32
BCW33



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	32	V
Collector-Emitter Voltage	V_{CEO}	32	V
Emitter-Base Voltage	V_{EBO}	5	V
Peak Pulse Current	I_{CM}	200	mA
Continuous Collector Current	I_C	100	mA
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	330	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER		SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Base - Emitter Voltage		V_{BE}	550		700	mV	$I_C=2mA, V_{CE} = 5V$
Collector-Emitter Saturation Voltage		$V_{CE(SAT)}$		120 210	250	mV mV	$I_C=10mA, I_B = 0.5mA$ $I_C=50mA, I_B = 2.5mA$
Base-Emitter Saturation Voltage		$V_{BE(SAT)}$		750 850		mV mV	$I_C=10mA, I_B=0.5mA$ $I_C=50mA, I_B=2.5mA$
Collector- Base Cut-Off Current		I_{CBO}			100 10	nA μA	$I_E=0, V_{CB}=20V$ $I_E=0, V_{CB}=20V, T_j=100^{\circ}C$
Static Forward Current Transfer Ratio	BCW31	h_{FE}	110	90	220		$I_C=10\mu A, V_{CE}=5V$ $I_C=2mA, V_{CE}=5V$
	BCW32	h_{FE}	200	150	450		$I_C=10\mu A, V_{CE}=5V$ $I_C=2mA, V_{CE}=5V$
	BCW33	h_{FE}	420	270	800		$I_C=10\mu A, V_{CE}=5V$ $I_C=2mA, V_{CE}=5V$
Transition Frequency		f_T		300		MHz	$I_C=10mA, V_{CE}=5V$ $f = 35MHz$
Collector Capacitance		C_{TC}			4	pF	$I_E = I_B = 0, V_{CB} = 10V$ $f = 1MHz$
Noise Figure		N			10	dB	$I_C = 200mA, V_{CE} = 5V$ $R_S = 2K\Omega, f = 1KHz$ $B = 200Hz$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$
Spice parameter data is available upon request for this device

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Diodes Incorporated:

[BCW31RTA](#) [BCW31RTC](#) [BCW31TA](#) [BCW31TC](#) [BCW32RTA](#) [BCW32RTC](#) [BCW32TA](#) [BCW32TC](#) [BCW33RTA](#)
[BCW33RTC](#) [BCW33TA](#) [BCW33TC](#)