



Wiha Precision ESD Safe Nut Drivers



277 Inch Nut Driver, With Precision ESD Safe Dissipative

Handle. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item									
No.	Inch	mm	Inch	mm	Inch	Inch	Inch	lbs.	pkg.
277 01	3/32	60	2.4	155	6.1	.16	.16	.04	10
277 03	7/64	60	2.4	155	6.1	.20	.20	.05	10
277 05	1/8	60	2.4	155	6.1	.20	.20	.05	10
277 07	9/64	60	2.4	155	6.1	.21	.24	.05	10
277 09	5/32	60	2.4	155	6.1	.22	.24	.05	10
277 11	3/16	60	2.4	155	6.1	.25	.28	.05	10
277 13	7/32	60	2.4	170	6.7	.30	.32	.06	10
277 15	1/4	60	2.4	170	6.7	.34	.36	.06	10

*Metric dimensions actual - Inch dimensions approximate



ESD standard
IEC 61340-5-1



277 91 Set 8 Pcs. Inch Nut Driver Precision ESD Safe Dissipative

Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

Item									
No.		Inch	mm		Inch	mm		lbs.	
277 91	277 01	3/32	60	277 09	5/32	60		.68	
	277 03	7/64	60	277 11	3/16	60			
	277 05	1/8	60	277 13	7/32	60			
	277 07	9/64	60	277 15	1/4	60			



277 Metric Nut Driver, With Precision ESD Safe Dissipative

Handle. Blade high alloy chrome-vanadium-molybdenum steel. Hard chromed finished. Handle manufactured from impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item									
No.	mm	mm	Inch	mm	Inch	Inch	Inch	lbs.	pkg.
277 20	1.5	60	2.4	140	5.5	2.5	3.0	.03	10
277 22	2.0	60	2.4	140	5.5	3.2	4.0	.04	10
277 25	2.5	60	2.4	140	5.5	4.0	4.0	.05	10
277 30	3.0	60	2.4	155	6.1	5.0	5.0	.06	10
277 35	3.5	60	2.4	155	6.1	5.3	6.0	.06	10
277 40	4.0	60	2.4	155	6.1	5.5	6.0	.06	10
277 45	4.5	60	2.4	155	6.1	6.2	7.0	.05	10
277 50	5.0	60	2.4	155	6.1	6.8	7.0	.06	10
277 55	5.5	60	2.4	170	6.7	7.6	8.0	.07	10
277 60	6.0	60	2.4	170	6.7	9.6	10.0	.06	10

*Metric dimensions actual - Inch dimensions approximate



ESD standard
IEC 61340-5-1



277 90 Set 8 Pcs. Metric Nut Driver Precision ESD Safe

Dissipative Handle Blade CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. In storage pouch

Item									
No.		mm	mm		mm	mm		lbs.	
277 90	277 20	1.5	60	277 35	3.5	60		.63	
	277 22	2.0	60	277 40	4.0	60			
	277 25	2.5	60	277 50	5.0	60			
	277 30	3.0	60	277 55	5.5	60			