

Simple function, 50 to 600W DC-DC converters

Features

- ◆ High Density
- ◆ Wide Range Input
- ◆ Output adjustment Capability
- ◆ Remote On/Off
- ◆ Fixed Switching Frequency
- ◆ International Safety Approvals
- ◆ Low component count



Key Market Segments & Applications



Specifications

Model		3.3V	5V	12V	15V	24V	28V	48V
Input range	VDC	24V nom: 18-36, 48V nom: 36-76V, 110V nom: 82-185V, 280V nom: 200-400V						
Output Voltage Adj. Range	VDC	2.97~3.63	4.5~5.5	10.8~13.2	13.5~16.5	21.6~26.4	25.2~30.8	43.2~52.8
Line Regulation	-	0.4% or 20mV (whichever is greater) over entire input range with constant load						
Load Regulation	-	0.8% or 40mV (whichever is greater) from no load to full load with constant input line						
Ripple and Noise	pk-pk	100mV		150mV		240mV	280mV	480mV
Series Operation	-	Possible - Refer to installation manual						
Over Voltage Protection	-	150 - 180%	125 - 145%					
Overload Protection	-	Approximately 105 - 140%, automatic recovery						
Remote On/Off	-	Low = ON, Open = OFF						
Remote Sensing	-	PH100S, PH150S, PH300S, PH600S models						
Parallel operation	-	PH300S & PH600S only: Requires external circuitry						
Inverter Good signal	-	PH300S & PH600S only: Signal available for status of inverter						
Thermal Protection	-	Internal sensing, self resetting						
Cooling	-	Conduction or forced air. See application notes for cooling and heatsink selection						
Operating Temperature Range	-	Baseplate temperature -20°C to +85°C (100°C on PH300 & PH600).						
	-	-40°C start up possible - consult factory						
Storage Temperature	-	-40°C to +85°C (+100°C on PH300 & PH600)						
Temperature Coefficient	-	0.02%/°C						
Isolation	-	Input to output: 3000VAC, Input to Baseplate: 2500VAC(1)						
Isolation Resistance	-	Output to Baseplate -100MOhm at 500VDC and 70%RH						
Safety Agency Approval	-	UL60950-1, CSA60950-1, EN60950-1 and CE Mark.						
Warranty	-	Two years						

Note: See Installation Manual for full details, test methods of parameters and application notes

Model Selector

Nominal Output Voltage (V)	Output Current (A)	Output Power (W)	24V input	48V input	110V input	280V input
3.3	10.0	33.0	-	PH50S48-3.3	-	PH50S280-3.3
3.3	15.0	49.5	-	PH75S48-3.3	-	PH75S280-3.3
3.3	20.0	66.0	-	PH100S48-3.3	-	PH100S280-3.3
3.3	30.0	99.0	-	PH150S48-3.3	-	PH150S280-3.3
3.3	50.0	165.0	-	-	-	PH300S280-3.3
3.3	100.0	330.0	-	-	-	PH600S280-3.3
5.0	10.0	50.0	PH50S24-5	PH50S48-5	PH50S110-5	PH50S280-5
5.0	15.0	75.0	-	PH75S48-5	PH75S110-5	PH75S280-5
5.0	20.0	100.0	-	PH100S48-5	-	PH100S280-5
5.0	30.0	150.0	-	PH150S48-5	PH150S110-5	PH150S280-5
5.0	50.0	250.0	-	-	-	PH300S280-5
5.0	100.0	500.0	-	-	-	PH600S280-5
12.0	4.2	50.0	PH50S24-12	PH50S48-12	PH50S110-12	PH50S280-12
12.0	6.3	75.0	-	PH75S48-12	PH75S110-12	PH75S280-12
12.0	8.4	100.0	-	PH100S48-12	-	PH100S280-12
12.0	12.5	150.0	-	PH150S48-12	PH150S110-12	PH150S280-12
12.0	25.0	300.0	-	-	-	PH300S280-12
12.0	50.0	600.0	-	-	-	PH600S280-12
15.0	3.4	50.0	PH50S24-15	PH50S48-15	PH50S110-15	PH50S280-15
15.0	5.0	75.0	-	PH75S48-15	PH75S110-15	PH75S280-15
15.0	6.7	100.0	-	PH100S48-15	-	PH100S280-15
15.0	10.0	150.0	-	PH150S48-15	PH150S110-15	PH150S280-15
15.0	20.0	300.0	-	-	-	PH300S280-15
15.0	40.0	600.0	-	-	-	PH600S280-15
24.0	2.1	50.0	PH50S24-24	PH50S48-24	PH50S110-24	PH50S280-24
24.0	3.2	75.0	-	PH75S48-24	PH75S110-24	PH75S280-24
24.0	4.2	100.0	-	PH100S48-24	-	PH100S280-24
24.0	6.3	150.0	-	PH150S48-24	PH150S110-24	PH150S280-24
24.0	12.5	300.0	-	-	-	PH300S280-24
24.0	25.0	600.0	-	-	-	PH600S280-24
28.0	1.8	50.0	PH50S24-28	PH50S48-28	PH50S110-28	PH50S280-28
28.0	2.7	75.0	-	PH75S48-28	PH75S110-28	PH75S280-28
28.0	3.6	100.0	-	PH100S48-28	-	PH100S280-28
28.0	5.4	150.0	-	PH150S48-28	PH150S110-28	PH150S280-28
28.0	10.8	302.0	-	-	-	PH300S280-28
28.0	21.5	602.0	-	-	-	PH600S280-28
48.0	6.3	302.0	-	-	-	PH300S280-48
48.0	12.5	600.0	-	-	-	PH600S280-48

Pinout

Pin Description	Function
-Vin	Negative Input Terminal
+Vin	Positive Input Terminal
+S	Positive Remote sense
-S	Negative Remote sense
+V	Positive Output Terminal
-V	Negative Output Terminal
IOG	Inverter Good Signal
TRIM	Output adjustment trim pin
CNT	On/Off Control Terminal
CS	Current Monitor Signal

Other DC-DC Products

PH Full Function	50 - 300W, full function versions of PH
PAQ, PAH, PAF	50 - 700W quarter, half & full bricks
PX	10-40W, 12-48V input, DC-DC
CC-E	1.5-30W, 5-48V input, DC-DC

For Additional Information, please visit
us.tdk-lambda.com/lp/products/ph-series-sf.htm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TDK-Lambda:

[PH100S280-12](#) [PH100S280-15](#) [PH100S280-24](#) [PH100S280-28](#) [PH100S280-3.3](#) [PH100S280-5](#) [PH100S48-12](#)
[PH100S48-15](#) [PH100S48-24](#) [PH100S48-28](#) [PH100S48-3.3](#) [PH100S48-5](#) [PH150S110-12](#) [PH150S110-15](#)
[PH150S110-24](#) [PH150S110-28](#) [PH150S110-5](#) [PH150S280-12](#) [PH150S280-15](#) [PH150S280-28](#) [PH150S280-3.3](#)
[PH150S280-5](#) [PH150S48-15](#) [PH150S48-28](#) [PH150S48-3.3](#) [PH300S280-12](#) [PH300S280-15](#) [PH300S280-28](#)
[PH300S280-3.3](#) [PH300S280-48](#) [PH300S48-12](#) [PH300S48-15](#) [PH300S48-3.3](#) [PH300S48-5](#) [PH50S110-15](#)
[PH50S110-5](#) [PH50S24-12](#) [PH50S24-24](#) [PH50S24-28](#) [PH50S24-5](#) [PH50S280-24](#) [PH50S280-3.3](#) [PH50S48-12](#)
[PH50S48-15](#) [PH50S48-24](#) [PH50S48-28](#) [PH50S48-3.3](#) [PH50S48-5](#) [PH600S280-12](#) [PH600S280-15](#) [PH600S280-24](#)
[PH600S280-28](#) [PH600S280-3.3](#) [PH600S280-48](#) [PH600S280-5](#) [PH75S110-15](#) [PH75S110-28](#) [PH75S110-5](#)
[PH75S280-12](#) [PH75S280-15](#) [PH75S280-28](#) [PH75S280-3.3](#) [PH75S280-5](#) [PH75S48-15](#) [PH75S48-24](#) [PH75S48-28](#)
[PH75S48-3.3](#) [PH75S48-5](#) [PH150S48-12](#) [PH50S24-15](#) [PH75S110-12](#) [PH50S280-15](#) [PH300S48-48](#) [PH300S280-5](#)
[PH150S280-24](#) [PH50S280-5](#) [PH75S48-12](#) [PH75S110-24](#) [PH75S280-24](#) [PH50S110-24](#) [PH50S280-12](#) [PH300S48-](#)
[24](#) [PH50S110-12](#) [PH150S48-24](#) [PH50S110-28](#) [PH150S48-5](#) [PH300S280-24](#) [PH50S280-28](#)