










CONNECTION DIAGRAM(BOTTOM VIEW)



GENERAL TOLERANCE

DIMENTION	TOLERANCE
Max. 1mm	±0.1
1mm~Max. 3mm	±0.2
Min. 3mm	±0.3

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	H.SASAKI	TE Connectivity			
			CHK	N.FUNAYAMA				
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD	A.NAGAI	NAME OUDH-D SPEC,000 CUSTOMER DRAWING				
			PRODUCT SPEC					
			APPLICATION SPEC					
			—					
MATERIAL —	FINISH —	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
			A3	00779	Ⓒ= 3-1440007-0	—		
CUSTOMER DRAWING						SCALE 4:1	SHEET 1 OF 2	REV B2

2						1		
LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

ⓑ

ⓑ

ⓑ

1461249-1	0UDH-SH-148D ,000	48V	0UDH-SH-148D	j
7-1419129-4	0UDH-SH-124D ,000	24V	0UDH-SH-124D	i
7-1419129-2	0UDH-SH-112D ,000	12V	0UDH-SH-112D	h
7-1419145-4	0UDH-SH-106D ,000	6V	0UDH-SH-106D	g
7-1419145-3	0UDH-SH-105D ,000	5V	0UDH-SH-105D	f
8-1419129-5	0UDH-SS-124D ,000	24V	0UDH-SS-124D	e
8-1419129-0	0UDH-SS-112D ,000	12V	0UDH-SS-112D	d
7-1419129-6	0UDH-SS-109D ,000	9V	0UDH-SS-109D	c
7-1419129-5	0UDH-SS-106D ,000	6V	0UDH-SS-106D	b
3-1440007-0	0UDH-SS-105D ,000	5V	0UDH-SS-105D	a
PART NO.	DESCRIPTION	PART B	PART A	ITEM

RELAY TYPE

NOTES
1.-SS-:PLASTIC SEALD TYPE
-SH-:WASHABLE TYPE

Ⓐ 2.LOT NO. SYSTEM AS FOLLOWING:

0811

WEEK
YEAR

DIMENSIONS: mm		DWN		TE Connectivity				
		CHK						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD		NAME 0UDH-D SPEC,000 CUSTOMER DRAWING				
		PRODUCT SPEC -						
MATERIAL		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779	DRAWING NO ©= 3-1440007-0	RESTRICTED TO -
		WEIGHT -						
		CUSTOMER DRAWING		SCALE 4:1		SHEET 2 OF 2		REV B2