








CATALOG LISTING  
1LS6-L  
PAGE 1 OF 1  
REPLACES  
PR-9854  
CHECK  
5 MAY 95  
JAF  
CHECK  
29 MAR 95  
GJW  
DRAWN  
FORMTEK

**MICRO SWITCH**  
a Honeywell Division  
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING  
1LS6-L



NOTES

- 1 - SWITCH IS ASSEMBLED FOR ACTUATION IN BOTH DIRECTIONS BUT MAY BE ADJUSTED TO ACTUATE IN EITHER THE CLOCKWISE DIRECTION ONLY OR THE COUNTERCLOCKWISE DIRECTION ONLY
- 2 - TO CONVERT SWITCH FOR ACTUATION IN EITHER THE CLOCKWISE OR COUNTERCLOCKWISE DIRECTION ONLY, REMOVE ACTUATOR HEAD AND ROTATE THE NOTCHED PLUNGER 90° TO THE RIGHT FOR CLOCKWISE ACTUATION OR 90° TO THE LEFT FOR COUNTERCLOCKWISE ACTUATION

4  
5  
6


SEAL TO BE FURNISHED BY USER  
ROLLER LEVER MAY BE LOCKED IN ANY POSITION THRU 360°  
LEVER FURNISHED UNASSEMBLED IN UNIT PACKING BOX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

| CHARACTERISTICS                            | ELECTRICAL DATA              |
|--------------------------------------------|------------------------------|
| OPERATING TORQUE -----27 IN.-OZ. MAX       | CONTACT ARRANGEMENT          |
| FULL OVERTRAVEL TORQUE -----36 IN.-OZ. MIN | (SEE CIRCUIT DIAGRAM)        |
| RELEASE TORQUE -----4.5 IN.-OZ. MIN        | L126 10A 125, 250 OR 480 VAC |
| PRETRAVEL -----20° MAX                     | 1/3HP 125 VAC, 3/4HP 250 VAC |
| DIFFERENTIAL TRAVEL -----12° MAX           | 0.8A 125 VDC, 0.4A 250 VDC   |
| OVERTRAVEL -----30° MIN                    |                              |
| FREE POSITION -----5° MIN                  |                              |
| BASIC SWITCH REPLACEMENT -----2MN1-L       |                              |



THIRD ANGLE PROJECTION



|                                           |
|-------------------------------------------|
| SCALE 1/2 TO 1                            |
| DO NOT SCALE PRINT                        |
| UNLESS OTHERWISE SPECIFIED TOLERANCES ARE |
| ONE PLACE (.0) ±.030                      |
| TWO PLACE (.00) ±.015                     |
| THREE PLACE (.000) ±.005                  |
| ANGLES ±                                  |
| WEIGHT                                    |