

5



4

3


2

1


(1:1)



Steckansicht n.
Contact face acc. to
IEC 61076-2-101



Leiterquerschnitt conductor cross section	0,14 - 0,34mm ² AWG26-AWG22
Kabeldurchmesser cable outside diameter	4,5 - 8,8mm



ALL Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maße/ Free size tolerances	
				Dat.	Name	Maßstab/Scale 2:1	M12-L RSV geschirmt, Stift, 4-polig, A-kodiert Circular Connector shielded, male, 4-pole, A-coded
EC01527	01.07.11	DY	Detail.	10.03.04	DY		
413867	13.05.08	DY	Insp.		SR		
412800	19.03.07	DY	Stand.				
411606	08.08.05	DY	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP				TB 21 03 221 1405
410925							
Mod.	Dat.	Name				Sub.	Blatt/ page

