



Order symbol: ABS 95/75 HG
Product nbr: 6081332
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074054722
El. number:
Finland 3421382
Denmark 8212023990

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:		L	W	H	Rating:
mm:		100	100	75	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:		3.9	3.9	3	
Materials:					
Material:		ABS			
Gasket material:		Polyurethane			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Cover screws material:		Polyamide			
Cover screws colour:		Grey			
Temperatures:					
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 95		Mounting plate (Galvanized steel)			
MIN 8		DIN-15 Mounting rail			
B-3		DIN-35 Mounting rail			
FP 22046		Wall fastening lug (4 pcs)			
Certificates:					
Fimko					
Europe EN 50298: 1998					
Gost R					

Certificates:

Fimko
Europe EN 50298: 1998
Gost R

