

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REVISED PER ECO-11-023039		21FEB12	KH	MS

MATERIAL:
HOUSING: NYLON, UL94V-0, BLACK.
TERMINALS: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC CHROMATE FINISH.


ELECTRICAL:
MAXIMUM CURRENT: 20A
OPERATING VOLTAGE: 600V
WIRE RANGE: 12-22 AWG

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C

1 ALL SCREWS BOTTOMED, TORQUE 2 TO 4 IN-LBS.



11.937	25	SSB7FG250102	2-1546968-5
11.500	24	SSB7FG240102	2-1546968-4
11.062	23	SSB7FG230102	2-1546968-3
10.625	22	SSB7FG220102	2-1546968-2
10.187	21	SSB7FG210102	2-1546968-1
9.750	20	SSB7FG200102	2-1546968-0
9.312	19	SSB7FG190102	1-1546968-9
8.875	18	SSB7FG180102	1-1546968-8
8.437	17	SSB7FG170102	1-1546968-7
8.000	16	SSB7FG160102	1-1546968-6
7.562	15	SSB7FG150102	1-1546968-5
7.125	14	SSB7FG140102	1-1546968-4
6.687	13	SSB7FG130102	1-1546968-3
6.250	12	SSB7FG120102	1-1546968-2
5.812	11	SSB7FF110102	8-796602-7
5.812	11	SSB7FG110102	1-1546968-1
5.375	10	SSB7FG100102	1-1546968-0
4.937	9	SSB7FG090102	1546968-9
4.500	8	SSB7FG080102	1546968-8
4.062	7	SSB7FG070102	1546968-7
3.625	6	SSB7FG060102	1546968-6
3.187	5	SSB7FG050102	1546968-5
2.750	4	SSB7FG040102	9-796602-8
2.312	3	SSB7FG030102	1546968-3
1.875	2	SSB7FG020102	1546968-2
1.437	1	SSB7FG010102	1546968-1
DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 11/16/06	 TE Connectivity					
		CHK S YODER 11/16/06						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER 11/16/06	NAME SSB7FGXX0102					
	0 PLC ± -	PRODUCT SPEC	-					
	1 PLC ± -	-	-					
	2 PLC ± .02	APPLICATION SPEC	-					
	3 PLC ± .010	-	-					
4 PLC ± -	ANGLES ± 1°	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-8-796602-7	RESTRICTED TO -		
MATERIAL -	FINISH -	CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1	REV B