

YA1C2LN

BURNDY® PRODUCTS

YA1C2LN

YA1C2LN : 1STR 2-HOLE SHORT NEMA



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)
[✉ Email Datasheet](#)
[🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)
[📄 > Sample request](#)
[€ > Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Length (Barrel)	Standard		
Size (Wire)	1 AWG		
Stud Hole (Size)	1/2 in.		
Stud Hole (Spacing)	1-3/4 in.		
Tongue Angle	Straight		
Tongue Width (in)	0.81 in.		
Wire Type	Commercial Stranded Copper		
Strip Length (in)	15/16 in.		
Physical			
Element A Index	11		
Approvals / Certifications			
UL Listed	Yes		
CSA Certified	Yes		
Other Features			
UPC	78181050042		
Keyword	ya		