



P		F	ZONE	LTR	REVISONS	
				DESCRIPTION	DATE	APP
				A	REVSD REDRAWN	
				B	REVSD/ECN CF-1706	07/88
				C	REV PER ECN CF1807 JPG	5-5-89
				D	ADDED 2-1,2-4,2-8,2-9,3-0,3-3 PER NPR 2901	5-7-90
				E	REV PER ECN BD4386	12-6-90
				F	ADDED 3-4 PER NPR 4061	3-16-92
				G	REV PER EC 0020-1041-93	12/02/93
				H	OB5 2--1,2--4,2--8,2--9,3--0,&3--3 PER EC 0020-933-93	03/16/94
				J	OBSOLETE -34	21 AUG 97
					PER EC 0410-197-96	JGH


- 1 UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- 2 PHOSPHOR BRONZE PER QQ-B-750.
- 3 PLATED WITH .000030 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.
- 5 UL RATED 94V-1 OR BETTER, THERMOPLASTIC, GRAY.



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL



OBSOLETE	1	.925	1.700	1.980	1.750	35	36	3-746288-4
OBSOLETE	5	1.125	2.100	2.380	2.150	43	44	3-746288-3
OBSOLETE	5	1.275	2.400	2.680	2.450	49	50	3-746288-0
OBSOLETE	5	1.025	1.900	2.180	1.950	39	40	2-746288-9
OBSOLETE	5	.875	1.600	1.880	1.650	33	34	2-746288-8
OBSOLETE	5	.525	.900	1.180	.950	19	20	2-746288-4
OBSOLETE	5	.275	.400	.680	.450	9	10	2-746288-1
	1	1.125	2.100	2.380	2.150	43	44	1-746288-3
	1	1.625	3.100	3.380	3.150	63	64	1-746288-2
	1	1.525	2.900	3.180	2.950	59	60	1-746288-1
	1	1.275	2.400	2.680	2.450	49	50	1-746288-0
	1	1.025	1.900	2.180	1.950	39	40	746288-9
	1	.875	1.600	1.880	1.650	33	34	746288-8
	1	.775	1.400	1.680	1.450	29	30	746288-7
	1	.675	1.200	1.480	1.250	25	26	746288-6
	1	.625	1.100	1.380	1.150	23	24	746288-5
	1	.525	.900	1.180	.950	19	20	746288-4
	1	.425	.700	.980	.750	15	16	746288-3
	1	.375	.600	.880	.650	13	14	746288-2