






CASE
ORIENTATION
TAB

REV.0

DCO 143317



RECOMMENDED
SOLDER PAD LAYOUT

COIL: @ 25°C

RESISTANCE 400 OHMS ±10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 9.0 VDC

MUST RELEASE

ENVIRONMENT:

VIBRATION 10 CPS TO 500 CPS @ 10 g's


SHOCK 30 g's 6±1 MS. DURATION

TEMPERATURE -55 °C TO +85 °C

NOTES: OPERATE TIME 4.0 MS MAX.

RELEASE TIME 6.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
1 AMP 28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 11/19/01

CK. TLG 11-20-01

CII Technologies
advanced control electronic solutions

CUST. CII

CUST. NO. STANDARD REV. ---

"SMGAD" RELAY

SHCD-12