






受控 CONTROLLED DOCUMENT					
编号 P/N	32-5964U L	版本 Rev	01	日期 Rel'd Date	SEP 14,09

DRAWING NO. 32-5964UL					
REVISIONS					
01	OFFICIAL RELEASE				
	08-20-09	Y	U	T	T
Betty's 08-24-26 + 08-07					



NOTES:

1. ELECTRICAL SPECIFICATIONS

INSULATION RESISTANCE: 1000 MEGOHMS
WITHSTAND VOLTAGE: 1000V,AC/ MINUTE

2. MECHANICAL SPECIFICATIONS

CONTACT MATERIAL: PHOSPHOR BRONZE 0.3MM THICKNESS
CONTACT PLATING: 50 MICRO-INCH GOLD PLATE OVER 100 MICRO-INCH NICKEL PLATING
HOUSING MATERIAL: POLYCARBNATE
DURABILITY: 1000 CYCLES MIN
UL FLAMABILY RATING: 94-V0

3. ENVIRONMENTAL SPECIFICATIONS

TEMPERATURE RANGE: -40 °C TO +70 °C

4. FOR SOLID OR STRANDED WIRE APPLICATIONS

5. FOR FLAT OVAL OR ROUND CABLE

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE	 Connectivity Solutions	
DECIMALS	mm	BETTY.YU	08-20-09		
X	± 0.5	CHECKED BY	DATE	TITLE	
X.X	± 0.15	TERRY.W	08-20-09		
X.XX	± 0.10	APPROVED BY	DATE	RJ11 MOD PLUG 50°U,STR,RND CBL	
ANGLES	± 0.5°	THOMAS	08-20-09		
U/M: mm		SHEET		DRAWING NO.	SIZE
THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.		1 OF 1		32-5964UL	C