

# SANDVIK BELZER

## Double hexagon Inch

DIN 3124/ISO 2725.

3/8" ● 10 DIN 3120/ISO 1174.

**Finish:** nickel and chrome-plated, fine-polished.


**Material:** VANADIUM-EXTRA.

High performance sockets, thin-walled, with Dynamic-Drive-Profile.

| Product code  | EAN code 731415+ |  | Dim. inch | L mm | D <sub>1</sub> mm | D <sub>2</sub> mm | T mm |  |
|---------------|------------------|-----------------------------------------------------------------------------------|-----------|------|-------------------|-------------------|------|------------------------------------------------------------------------------------|
| A7400DZ-1/4   | 1759193          | 5                                                                                 | 1/4       | 28   | 9,5               | 17,2              | 6,5  | 15                                                                                 |
| A7400DZ-5/16  | 1759278          | 5                                                                                 | 5/16      | 28   | 11,5              | 17,2              | 8,5  | 16                                                                                 |
| A7400DZ-3/8   | 1759438          | 5                                                                                 | 3/8       | 28   | 13,5              | 17,2              | 10,5 | 19                                                                                 |
| A7400DZ-7/16  | 1759513          | 5                                                                                 | 7/16      | 28   | 15,5              | 17,2              | 11,5 | 21                                                                                 |
| A7400DZ-1/2   | 1759780          | 5                                                                                 | 1/2       | 28   | 17,5              | 17,2              | 12,5 | 22                                                                                 |
| A7400DZ-17/32 | 1819866          | 5                                                                                 | 17/32     | 32   | 18,5              | 17,2              | 14,5 | 23                                                                                 |
| A7400DZ-9/16  | 1759865          | 5                                                                                 | 9/16      | 32   | 19,5              | 17,2              | 14,5 | 25                                                                                 |
| A7400DZ-19/32 | 1819873          | 5                                                                                 | 19/32     | 32   | 20,5              | 18                | 14,5 | 26                                                                                 |
| A7400DZ-5/8   | 1819880          | 5                                                                                 | 5/8       | 32   | 21,4              | 19                | 14,5 | 28                                                                                 |
| A7400DZ-11/16 | 1819897          | 5                                                                                 | 11/16     | 35   | 23,4              | 20,5              | 17   | 30                                                                                 |
| A7400DZ-3/4   | 1819903          | 5                                                                                 | 3/4       | 35   | 25,4              | 22                | 17,5 | 40                                                                                 |
| A7400DZ-13/16 | 1819910          | 5                                                                                 | 13/16     | 35   | 27,4              | 23,5              | 17,5 | 44                                                                                 |
| A7400DZ-7/8   | 1819927          | 5                                                                                 | 7/8       | 38   | 29,4              | 24,5              | 19,5 | 50                                                                                 |



A7400DZ




These sockets are applicable to all nuts and bolts used in the aerospace industry.

|     |                                                           |
|-----|-----------------------------------------------------------|
| DIN | 65546, 65438 - 65443,                                     |
| LN  | 29520, 29542, 29550, 29551, 29769, 29901 - 29903, 29934,  |
|     | 29955, 65056, 65101 - 65106, 65416 - 65418, 29529, 29894, |
|     | 29919, 65414,                                             |
| VLN | 29953,                                                    |
| EN  | 2907, 3013.                                               |

### Dynamic-Drive-Profile

Low surface pressure due to large force-applying surfaces



No notching sensitivity