


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MAX BUNDLE DIA.	PACKAGE QTY	LENGTH L ±.3 [ 7 ]
MLT2LH-LP	2" [ 51 ]	50	7.9" [ 201 ]
MLT4LH-LP	4" [ 102 ]	50	14.3" [ 362 ]
MLT6LH-LP	6" [ 152 ]	50	20.5" [ 521 ]
MLT8LH-LP	8" [ 203 ]	50	26.8" [ 679 ]



NOTES:

- APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, AND HTMT
- MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS) WHEN TESTED ON A 1 1/2" MANDREL
- BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
- TOLERANCES:  
 .XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
 .X = ±.03 [ .8 ]        ANGLES = ±2°

REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
03A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY				JAMB	DPN	2x	N41126BS_DC
02	8/04	JAMB	DPN	Ⓟ REMOVED "AISI NO.1 FULL RADIUSED" & REPLACED WITH "FULLY ROUNDED"	11907	CCH	JJB				
01	10/03	BRH	DPN	Ⓐ ADDED ST3MT TO APPLICATION TOOLS NOTE	11162	CCH	JJB				
00	6/03	JAMB	DPN	RELEASED	10544	CCH	JJB				

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

METAL LOCKING TIE  
 LIGHT/HEAVY SERIES - 304 STAINLESS STEEL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[MLT4LH-LP](#)