

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731010120](#)
Status: **Active**
Description: BNC 75 OHm, Right Angle PCB Bulkhead Jack Receptacle with Board Locks, Low Profile

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-73598-0051 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family RF/Coax Connectors
Series [73101](#)
Comments Low Profile
More Detailed Tech Information rf@molex.com
Product Name BNC
Style PCB
Wire/Cable Type N/A


Physical
Cable Attachment N/A
Gender Female
Keying to Mating Part N/A
Orientation Right Angle
PCB Mounting Through Hole
PCB Thickness Recommended (in) 0.125 In
PCB Thickness Recommended (mm) 3.20 mm
Packaging Type Tray
Panel Mount Yes
Panel Mount Method Bulkhead
Reverse Polar No

Electrical
Impedance 75 ohms

Solder Process Data
Duration at Max. Process Temperature (seconds) 5
Lead-free Process Capability Wave Capable (TH only)
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 245

Material Info

Reference - Drawing Numbers
Product Specification PS-73598-0051
Sales Drawing SD-73101-0120



EU RoHS
RoHS Compliant RF Product
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Not Reviewed



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[73101Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION