


Coin Type Polyacene Capacitors

PAS311SR-VA6R



■ Features

- Item Summary
2.6V, 11 μ Ah(Measured between 2.6V-1.5V), 0.035F, 70 Ω
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Tape&Reel 4000pcs

■ Products characteristics table

Temperature Range	-25 to +70°C
Maximum Usable Voltage	2.6V
Nominal Capacity	11 μ Ah(Measured between 2.6V-1.5V) 0.035F
Internal Resistance	70 Ω
Initial Capacitance	- More than 0.025F
Initial Internal Resistance	Less than 120 Ω
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.

2014.05.23