



80-series, Phosphated, 80

As per DIN 3117 Form A, angle 15°, BS 6333, ISO 6787 and ASME B107.8M-1996.

Finish: Phosphated. Precision-hardened and anti-corrosion treated.

Series P: combination of pipe grip facility, one side serrated, may be used as a pipe wrench. Left-reading, measurement scale in mm.

IP = Industrial pack



			A mm	B mm	C mm	D mm	
8069	0007028	5	110	13	4.0	9.0	60
8070	0007110	5	155	20	4.9	11.3	135
8071	0007202	5	205	27	6.0	12.9	255
8072	0007288	5	255	30	8.6	15.5	400
8072 P	0042524	5	255	33	8.6	15.5	400
8073	0007363	5	305	34	11.9	18.0	665
8073 P	0101610	5	305	35	11.9	18.0	680
8074	0007448	3	380	44	14.0	20.0	1035
8075	0007523	3	455	53	17.7	22.5	1665
8069 IP	0007042	50	110	13	4.0	9.0	60
8070 IP	0007134	40	155	20	4.9	11.3	135
8071 IP	0007226	50	205	27	6.0	12.9	255
8072 IP	0007301	30	255	30	8.6	15.5	400
8072 P IP	0046522	30	255	33	8.6	15.5	400
8073 IP	0007387	20	305	34	11.9	18.0	665
8074 IP	0007462	20	380	44	14.0	20.0	1035
8075 IP	0007547	12	455	53	11.7	22.5	1665