


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



T568B WIRING SCHEME	
PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

NOTES:

1. TERMINATED WITH (8 POSITION) UTP MODULAR PLUGS ON BOTH ENDS PER T568B.
2. CONSTRUCTED WITH 4-PR/26AWG STRANDED F/UTP CAT6A PATCH CABLE
3. MATERIAL:
PLUG: POLYCARBONATE
BOOT: THERMOPLASTIC RESIN
4. FLAMMABILITY RATING: CM/LSZH DUAL RATED

CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
GRAY	GY

PANDUIT PART NUMBER	MIN. CABLE LENGTH
NK6APC3**	3 FT
NK6APC5**	5 FT
NK6APC7**	7 FT
NK6APC10**	10 FT
NK6APC14**	14 FT
NK6APC20**	20 FT
NK6APC1M**	1 METER
NK6APC2M**	2 METERS
NK6APC3M**	3 METERS
NK6APC4M**	4 METERS
NK6APC5M**	5 METERS
NK6APC7M**	7 METERS
NK6APC10M**	10 METERS
NK6APC15M**	15 METERS

PART NUMBER		NK6APCXX**	
TITLE			
NETKEY CATEGORY 6A UTP PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		14M504BB/00	
DATASET FILE NAME		14M504BB_DC02/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XXX ± .010 [.3] .XX ± .03 [.8]		SEE NOTE 3	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
14M504BB-02		14M504BB-02	
DRAWN BY	DATE	CHK	SCALE
BJN	10-21-14	SCAL	NONE
SHT 1 OF 1			SIZE
			A