



92x92x25mm Series

Power supply, UPS, network, server, power rack, home appliance and test instruments...etc.

EXTERNAL DIMENSIONS



Housing	Impeller	Bearing Available	Lead Wire	Protection	Operating Temp*	Voltage Available
Plastic (UL: 94V-0)	Plastic (UL: 94V-0)	Ball/Hydro/Sleeve	UL1007 AWG24	Current Limit	-10°C~70°C	12V, 24V

*: -10°C~60°C for fans with sleeve/ball combination bearings.

SPECIFICATIONS (NOMINAL)

Frame Size	Model No.	Bearing type	Voltage (V)	Current (A)	Power (W)	Speed (rpm)	Air flow (CFM)	Pressure (mmAq)	Noise (dB/A)	Weight (g)
92x92x25mm	AD0912UX-A71GL	Hypro	12	0.39	4.68	3200	57.8	3.96	38.6	103
92x92x25mm	AD0912UB-A71GL	Ball	12	0.39	4.68	3300	60.0	4.15	39.4	103
92x92x25mm	AD0912HX-A70GL	Hypro	12	0.25	3.00	2700	50.0	2.93	33.7	103
92x92x25mm	AD0912HB-A70GL	Ball	12	0.25	3.00	2900	52.5	3.32	35.0	103
92x92x25mm	AD0912MX-A70GL	Hypro	12	0.17	2.04	2400	43.5	2.34	31.3	103
92x92x25mm	AD0912MB-A70GL	Ball	12	0.17	2.04	2600	47.2	2.69	32.7	103
92x92x25mm	AD0912LX-A70GL	Hypro	12	0.12	1.44	2100	37.9	1.87	26.5	103
92x92x25mm	AD0912LB-A70GL	Ball	12	0.12	1.44	2300	41.6	2.18	29.8	103
92x92x25mm	AD0924UX-A71GL	Hypro	24	0.21	5.04	3200	57.8	3.96	38.6	103
92x92x25mm	AD0924UB-A71GL	Ball	24	0.21	5.04	3300	60.0	4.15	39.4	103
92x92x25mm	AD0924HX-A70GL	Hypro	24	0.15	3.60	2700	50.0	2.93	33.7	103
92x92x25mm	AD0924HB-A70GL	Ball	24	0.15	3.60	2900	52.5	3.32	35.0	103
92x92x25mm	AD0924MX-A70GL	Hypro	24	0.12	2.88	2400	43.5	2.34	31.3	103
92x92x25mm	AD0924MB-A70GL	Ball	24	0.12	2.88	2600	47.2	2.69	32.7	103
92x92x25mm	AD0924LX-A70GL	Hypro	24	0.08	1.92	2100	37.9	1.87	26.5	103
92x92x25mm	AD0924LB-A70GL	Ball	24	0.08	1.92	2300	41.6	2.18	29.8	103

Specifications subject to change without notice.

* Noise is measured at the distance of one (1) meter from the axis of intake.

PERFORMANCE CURVES

* MOTOR PROTECTIVE CIRCUIT AND THIRD LEAD WIRE

0	1	2	3	4	6	7	8	9	A
✓	✓	✓	✓	✓	✓	✓		✓	

* SAFETY APPROVALS

✓	✓	✓	✓

