





REV.	DATE	ECR NO.	DESCRIPTION
NC	12/12/05	—	INITIAL RELEASE
A	10/14/08	—	REVISE OVERALL LENGTH TO 20.25



NOTE:

1. MAX. PANEL THICKNESS = 7.5mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS DATE	Amphenol Connex							
8						DRAWN GRS	10/14/08	PART DESCRIPTION SMA BULKHEAD P.C. MOUNT JACK						
7						CHECKED								
6						ISSUED								
5	HEX NUT	BRASS	GOLD	1		SHEET 1 OF 1								
4	LOCK WASHER	BRASS	GOLD	1				PART NO.	132291-12					
3	CONTACT PIN	BER. COPPER	GOLD	1				DWG. NO.	132291-12.DWG			REV. A	SIZE A	SCALE NA
2	INSULATOR	PTFE	NATURAL	1										
1	BODY	BRASS	GOLD	1										
	DESCRIPTION	MATERIAL	FINISH	QTY										