



Timer components One-way in-line fixed flow restrictors Part number 81529003




• XXX

	Type	Flow at 4 bars Nm3/h	Ø orifice (mm)	Colour
81529003	One-way in-line fixed flow restrictors	0,18 →0,30	0,3	white
81529004	One-way in-line fixed flow restrictors	0,35 →0,50	0,4	yellow
81529005	One-way in-line fixed flow restrictors	0,58 →0,77	0,5	red
81529006	One-way in-line fixed flow restrictors	0,80 →1,06	0,6	green
81529007	One-way in-line fixed flow restrictors	1,10 →1,39	0,7	blue
81529008	One-way in-line fixed flow restrictors	1,45 →1,65	0,8	grey
81529010	One-way in-line fixed flow restrictors	2,30 →2,80	1	black
81529025	One-way in-line fixed flow restrictors	0,08 →	0,25	white
81525101	One-way adjustable flow restrictorFree low 30	81 525 101.		
81526001	One-way adjustable flow restrictorFree low 200	81 526 001.		
79452808	Capacity for timing 10 60 s	79 452 808		


Symbol

Opened flow Nl/min	Depending on orifice
Orifice diameter mm	-
Operating pressure (bar)	1 →8
Delay (s)	-
Capacity cm ³	-
Connection - Sub-base	•
Push-in connection for semi-rigid tubing (NFE 49100) mm	Ø 4
Weight (g)	8

Dimension Diagram : 81 529



: *** TRADUCTION MANQUANTE ***



N°	Legend
1	
2	
3	

: One-way with fixed flow

