

## Electronic Hour Meter, AC Hour Meter T50 Series



T50A2, T50B2

### Features

- Low Power Consumption
- Solid State Electronic Drive Circuit
- Quartz-Crystal for Accurate Timing
- Non-reset
- UL/cUL Recognized, CE & RoHS Compliant
- High Impact, Tamperproof Plastic Case
- IP65
- Indicates Operating Time in Hours and Tents
- No Battery Back-Up Required
- Quiet operation
- MADE IN THE U.S.A.

ENM's Series T50 electronic AC hour meter is a low cost reliable hour meter incorporating the latest state-of-the-art in electronics. It's quartz-crystal time base insures accurate long term time-keeping. A reliable electromechanical wheel-type indicator is used to store accumulated hours.


This compact tamperproof meter is sealed against the environment to provide years of service.

The T50 elapsed time indicator was designed for use on test and recording equipment, for providing maintenance control, for establishing warranty programs, for measuring machine utilization and production time, or for any application where time-in-use is to be determined.

### Specifications

Time Scale:	6-digits 99,999.9 Hours Automatic recycle to zero
Figures:	Hours - White on black Tenths - Red on white Height - 0.140"
Operation Voltage:	230, 115, 48, 24 VAC $\pm 10\%$ 50/60 Hz Other voltage available
Power Consumption:	Less than 0.4 Watts
Accuracy:	Better than $\pm 0.02\%$ over entire range
Temperature:	-40°F to +185°F (-40°C to +85°C)
Vibration Resistance:	Withstands 10-80 Hz at 20g's max. (SAE J1378)
Shock:	55g at 9-13 ms (SAE J1378)
Humidity:	95% (SAE J1378)
Terminations:	1/4" male blade terminals
Configuration:	Round SAE Bezel with new push-on retaining ring Round 3-Hole Bezel

### T50 Series



2013 ENM Co.®

#### LIMITED WARRANTY

ENM Company resettable electromechanical counters are warranted to the consumer to be free from defects in material and workmanship for a period of 3 years. All ENM products which fall within the warranty period due to defects in material or workmanship will be repaired or replaced, at ENM's option, without charge to the consumer when returned with proof of purchase to any authorized ENM dealer in the United States, transportation charges prepaid, provided there is no evidence of improper installation, tampering, or other abuse. All implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, shall be limited in duration to the express warranty period specified above. ENM disclaims any liability for consequential damages due to breach of any written or implied warranty on its products. Datasheet information subject to change.