


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	"A" (IN.) MIN.	"B" (IN.)	"C" +/- .031 (IN.)	MATERIAL	COLOR
T100X000YP1	1200	1.00	0.125	GMY3THERM750	WHITE
T200X000YP1	1200	2.00	0.125	GMY3THERM750	WHITE
T400X000YP1	1200	4.00	0.125	GMY3THERM750	WHITE

NOTES:
1. RESIN RIBBON RECOMMENDED.



										CAD FILENAME/LAYERS 121043AA_DS_C10990/01EA		
										PANDUIT CORP. TINLEY PARK, ILLINOIS		
										SUPER-TACK POLYESTER TAPES		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.062 (.XXX) ±.015 (.XX) ±.031 ANGLES ± 1		
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION		
										DRAWN BY EOY		
										DATE 05-04-12		
										MAT'L: SEE TABLE		
										SCALE NTS		
										DRAWING NO. C10990		
										DWG B SIZE		
A	05/04/12	EOY	DRAWING RELEASE									
REV	DATE	BY	CHK	DESCRIPTION				ECN	-	R	CUST	SUP