




REV.	DATE	DESCRIPTION
NC	12/01/05	INITIAL RELEASE



NOTE:
1. MAX. BOARD THICKNESS = 1.57mm

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
7						DRAWN	G.R.S.	12/01/05								
6						CHECKED										
5	HEX NUT	BRASS	GOLD	1						PART DESCRIPTION						
4	LOCK WASHER	BRASS	GOLD	1						SMA END LAUNCH RECEPTACLE JACK						
3	CONTACT PIN	BER. COPPER	GOLD	1						PART NO.						
2	INSULATOR	TEFLON	NATURAL	1						132371						
1	BODY	BRASS	GOLD	1						DWG. NO.		132371.DWG	REV. NC	SIZE A	SCALE NA	
	DESCRIPTION	MATERIAL	FINISH	QTY					CAD FILE		C:/132/132371.DWG					