

Large Size – Alloys

LS-1800 and LS-1900 Series are a Step Above Our Plastic Units for Pressure Capabilities

Excellent stability for general use in oils and water.

LS-1800 Series –
Buna N Float



LS-1800 Series –
Teflon® Float



LS-1900 Series –
Buna N Float



Intermediate in size, LS-1800 switches provide long life and dependability to meet a broad range of requirements.

With large float displacement, switch withstands rough service; is suitable for high viscosity liquids.

Dimensions

LS-1800 Series		LS-1900 Series
Buna N Float	Teflon® Float	Buna N Float

†L₁ = Switch actuation level, nominal (based on a liquid specific gravity of 1.0).

Common Specifications

Electrical Termination: No.18 AWG, 24~ L., Polymeric Lead Wires.

Approvals: All Switches on this page are U.L. Recognized – File No. E45168, and are CSA Listed – File No. 30200.

Switch Operation: Selectable, N.O. or N.C., by inverting float on unit stem (except for LS-1800 Series switch with Teflon® float). Units are shipped N.O. unless otherwise specified.

How To Order – Select Part Number based on specifications required.

Material				Min. Liquid Sp. Gr.	Operating Temperature	Pressure, PSI, Max.	Switch* SPST	Part Number
Series Number	Stem and Mounting	Float	Other Wetted					
LS-1800	Brass	Buna N	316 Stainless Steel, Hysol	.75	Water: to 180°F (82°C) Oil: -40°F to +230°F (-40°C to +110°C)	150	20 VA	01801 ⚡
		Buna N		.75			100 VA**	35651 ⚡
	316 Stainless Steel	Buna N		.65			20 VA	01807 ⚡
		Teflon®		.65			100 VA**	35657 ⚡
LS-1900	Brass	Buna N	316 Stainless Steel, Hysol	.55	Water: to 180°F (82°C) Oil: -40°F to +230°F (-40°C to +110°C)	150	20 VA, N.O.	01811 ⚡
		Buna N		.55			20 VA	01901 ⚡
	316 Stainless Steel	Buna N		.55			100 VA***	35676 ⚡
		Buna N		.55			20 VA	01907 ⚡
							100 VA	35682 ⚡

*See "Electrical Data" on Page X-5 for more information.

*** LS-1900 100VA unit is UL Resistive Rated.

**LS-1800 100 VA switches are not U.L. Recognized.