




RF179-74BJ3-72RP1-0200

75Ω OPTIMIZED RG 179 CABLES

SPECIFICATIONS

For complete specifications see www.samtec.com?RF179

RF Connector:

Outer Contact Material:

Ni plated Brass

(BNC)

Au plated Brass

(SMB)

Au plated BeCu

(MCX, MMCX7, DIN)

Center Contact Material:

Au plated Brass

(BNC-P, MCX, MMCX7)

Au plated BeCu

(SMB)

Au plated Copper Alloy

(DIN, BNC-J)

Insulator Material:

PTFE

Operating Temperature:

-50°C to +165°C

Impedance:

75Ω

Frequency Range:

0~4 GHz *

(Cable & connector dependent)

RoHS Compliant:

Yes

RG 179 Cable:

Impedance:

75Ω ±3Ω

Capacitance:

64pF/meter

Propagation Delay:

4.83 nsec/meter

Max Attenuation

(cable only):

0.8dB @ 1GHz for 1 meter

Conductor Size:

30 AWG, (0,31 mm) .012" dia.

Conductor Material:

Silver Plated Copper

Conductor Resistance:

0.34Ω/meter max

Current Rating:

3A DC

Insulator Diameter:

(1,6 mm) .063"

Insulator Material:

PTFE

Dielectric Constant:

1.8 dK

Shield Material:

Silver Plated Copper

Jacket Material:

FEP

Jacket Diameter:

(2,54 mm) .100"

Jacket Temp Rating:

-55°C to +165°C

Jacket Color:

Amber


RoHS Compliant:

Yes

Mates with:
BNC7T, MCX7, MMCX7,
SMB7H, DIN7A

THINK OUTSIDE THE CATALOG

- Create a full system: cable assembly and board level mates, 50Ω and 75Ω solutions
- 24-hour samples on standard products
- Visit: rf.samtec.com



30 AWG
75Ω RG 179
coax cable

Standard
Heat Shrink

Single or Double
Ended

CABLE TYPE


END 1 CONNECTOR

END 2 CONNECTOR

RF179

= RG 179 Cable

Specify END OPTIONS from chart



END OPTIONS		END OPTIONS	
-73SP4 = 75Ω MMCX7 Straight Plug (10μ" (0,25 μm) Gold on Center Contact, Gold Flash on Shell)		-72RP1 = 75Ω MCX Right Angle Plug (30μ" (0,76 μm) Gold on Center Contact, Gold Flash on Shell)	
-73RP1 = 75Ω MMCX7 Right Angle Plug (30μ" (0,76 μm) Gold on Center Contact, Gold Flash on Shell)		-72SP1 = 75Ω MCX Straight Plug (30μ" (0,76 μm) Gold on Center Contact, Gold Flash on Shell)	
-73SJ4 = 75Ω MMCX7 Straight Jack (10μ" (0,25 μm) Gold on Center Contact, Gold Flash on Shell)		-77SP1 = 75Ω SMB Straight Plug (30μ" (0,76 μm) Gold on Center Contact, Gold Flash on Shell)	

* See connector component pages for specific range.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM



RF179-78SP4-77SP1-0200



RF179-72SP1-73SJ4-0100

RF179 SERIES



Wide variety of 75Ω end options including BNC, MCX and SMB

Straight or Right Angle terminations



ALSO AVAILABLE (MOQ Required)

- Additional stripping and tinning options
 - Additional plating options
 - Additional end connector combinations
- Contact Samtec.

OTHER SOLUTIONS

- Cable connector kits (see cable components catalog pages)

OVERALL LENGTH

—“XXXX”

= Overall Length in millimeters -0100 (100 mm) 3.94" minimum

STRIPPED & TINNED (Dimensions in mm)

CALLOUT	A	B	C
-303030	3.0	3.0	3.0
-303040	3.0	3.0	4.0
-403030	4.0	3.0	3.0
-403040	4.0	3.0	4.0
-404040	4.0	4.0	4.0

Both center conductor and braid shield are stripped, only the center conductor is tinned.

END OPTIONS

-77RP1 = 75Ω SMB Right Angle Plug (30μ" (0,76 μm) Gold on Center Contact, Gold Flash on Shell)	
-74SP3 = 75Ω BNC Straight Plug -D4SP3 = 75Ω BNC Die Cast Straight Plug (10μ" (0,25 μm) Gold on Center Contact, Nickel on Shell)	
-74BJ3 = 75Ω BNC Bulkhead Jack (10μ" (0,25 μm) Gold on Center Contact, Nickel on Shell)	

END OPTIONS

-78SP4 = 75Ω DIN Straight Plug (10μ" (0,25 μm) Gold on Center Contact, Nickel on Shell)	
-SING = Single Ended (End 2 callout)	
XXXXXX = Stripped & Tinned (End 2 callout)	

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685