

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [31067-1040](#)  
**Status:** **Active**  
**Overview:** [H-DAC 64™ Unsealed Connector System](#)  
**Description:** 2.54mm H-DAC 64™, 3 Way Male Housing Assembly, Single Row, Polarization A

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Product Specification PS-34646-001 \(PDF\)](#)  
[Application Specification AS-31067-100 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                |                                                     |
|----------------|-----------------------------------------------------|
| Product Family | Crimp Housings                                      |
| Series         | <a href="#">31067</a>                               |
| Application    | Power, Wire-to-Board                                |
| Comments       | Polarization Option A, Black                        |
| Overview       | <a href="#">H-DAC 64™ Unsealed Connector System</a> |
| Product Name   | H-DAC 64™                                           |
| UPC            | 800756062969                                        |

**Physical**

|                               |                                 |
|-------------------------------|---------------------------------|
| Circuits (maximum)            | 3                               |
| Circuits Detail               | 3                               |
| Color - Resin                 | Black                           |
| Gender                        | Male                            |
| Glow-Wire Compliant           | No                              |
| Keying to Mating Part         | None                            |
| Lock to Mating Part           | Yes                             |
| Material - Resin              | Modified Polystyrene, Polyester |
| Net Weight                    | 1.692/g                         |
| Number of Rows                | 1                               |
| Packaging Type                | Bag                             |
| Panel Mount                   | No                              |
| Pitch - Mating Interface      | 2.54mm                          |
| Pitch - Termination Interface | 2.54mm                          |
| Polarized to Mating Part      | Yes                             |
| Ports                         | 1                               |
| Stackable                     | No                              |
| Temperature Range - Operating | -40°C to +100°C                 |


**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 11A, 9A |
|-------------------------------|---------|

**Material Info**

**Reference - Drawing Numbers**

|                           |              |
|---------------------------|--------------|
| Application Specification | AS-31067-100 |
| Product Specification     | PS-34646-001 |
| Sales Drawing             | SD-31110-003 |



**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[31067Series](#)

**Mates With**  
[31101](#) HDAC 64™ Vertical Header

**Use With**  
See Product Spec

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

31067-1040