


Dimensions: mm (in.)

**Mechanical Specifications:**

- Operating Frequency: 120 operations
- Life: 1,000,000 operations min.
- Operating Temperature: 0°C ~ 65°C
- Storage Temperature: -25°C ~ 85°C

Note:

- RoHS Compliant and process compatible with 260° solder

Electrical Specifications:

- Rating: 3A/125VAC; 0.2A/60VDC
- Operating Frequency: 10~30 operations
- Contact Resistance (initial): 30~100mΩ max.
- Insulation Resistance (at 500VDC): 100MΩ min.
- Dielectric Strength: 1,000VAC RMS (50-60HZ)
- Life (at rated load): 6,000~15,000 operations

Operating Characteristics:

- OF Max. (g): 70
- OP (mm): 7.9±0.8
- PT Max. (mm): 3.4
- OT Min. (mm): 0.6
- MD Max. (mm): 1.0
- FP Max. (mm): 10.5
- RF Min. (g): 10

Super-Miniature Snap Switch
101-13-03-070ST-EV

**Mountain
Switch**

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-13-03-070ST-EV](#)