



DIN 338/BS 328

Point angle

135° split point

Surface treatment

Bronze

Application

For steels of high tensile strength, stainless and heat resistant steels.

524104

Size (mm)	Flute length (mm)	Overall length (mm)	Order code	Price each
1.0	12	34	155-4319	— —
1.5	18	40	155-4320	— —
2.0	24	53	155-4321	— —