



KT

Inserts, large



KT / KT-DPF large



KTMB large

1

Product description

Cable inserts KT large accept a wide range of cable diameters from 16 to 34 mm. They are used with the following cable entry frames:

- KEL(-ER) | Page 6 - 17
- KVT | Page 24 - 28
- KEL 183 | Page 38




ATG adapter inserts provide the possibility to hold a small KT insert to reduce the clamping range down to 2 mm.

Specification KT grey

Material Elastomer
Flame class UL94-Vo, self-extinguishing
Temperature - 40°C to + 90°C (static)
Properties Halogen free, silicone free

Specification KT black

Material Elastomer
Flame class UL94-HB
Temperature - 30°C to + 90°C (static)
Properties Higher chemical resistance, UV-stabilised

Description	Type	Order No. grey	Order No. black	Clamping range	PU
	ATG	41253	41353	Adapter insert	10
	BTG	41252	41352	Blind insert or 5 - 20 mm	10
	KT 16	41216	41316	16 - 17 mm	10
	KT 17	41217	41317	17 - 18 mm	10
	KT 18	41218	41318	18 - 19 mm	10
	KT 19	41219	41319	19 - 20 mm	10
	KT 20	41220	41320	20 - 21 mm	10
	KT 21	41221	41321	21 - 22 mm	10
	KT 22	41222	41322	22 - 23 mm	10
	KT 23	41223	41323	23 - 24 mm	10
	KT 24	41224	41324	24 - 25 mm	10
	KT 25	41225	41325	25 - 26 mm	10
	KT 26	41226	41326	26 - 27 mm	10
	KT 27	41227	41327	27 - 28 mm	10
	KT 28	41228	41328	28 - 29 mm	10
	KT 29	41229	41329	29 - 30 mm	10
	KT 30	41230	41330	30 - 32 mm	10
	KT 32	41232	41332	32 - 33 mm	10
	KT 34	41234	41334	33 - 34 mm	10

*Only valid for grey product types