



DCD935B2-GB

14.4 Volt 13 mm XRP Heavy Duty Cordless Hammerdrill

Selling Proposition

- Powerful 14.4 Volt XRP Combi tool for heavy duty drilling and screwdriving applications
- DEWALT built frameless motor reduces size and increases efficiency producing excellent runtime
- Ultra smooth 3 speed selector for optimum performance in high torque, normal use and high speed applications.
- 22 position adjustable torque control for uniform results and optimised precision when screwdriving
- 13 mm self tightening keyless chuck with automatic spindle lock for ultimate bit control
- Extra sensitive trigger increases control when setting and removing fasteners

Standard Equipment

- 40 minute multi chemistry charger
- 2 batteries
- Multi position side handle
- Heavy duty carrying case

Warranty Specifications

- 1 year free service contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Voltage	14.4 V
Battery Capacity	NiMH 2.6 Ah
Chuck Capacity	1.5-13 mm
Power Output	350 Watts
No Load Speed	0-450 / 0-1500 / 0-1800 rpm rpm
Beats per Minute	0-7650 / 0-25500 / 0-30600 bpm bpm

DCD935B2-GB

Specifications	
Max Torque	50 Nm
Max. Drilling Capacity [Wood]	50 mm
Max. Drilling Capacity [Metal]	13 mm
Max. Drilling Capacity [Masonry]	16 mm
Weight	2.66 kg
Length	245 mm
Height	247 mm