


D-Sub Connector PC Pins

152-5209, 152-5215, 152-5225, 152-5237, 152-5250,
152-5309, 152-5315, 152-5325, 152-5337, 152-5350

KOBICONN

DIMENSIONS: In.



ELECTRICAL SPECIFICATIONS

Current rating:	5AWG cable
Wire size:	20AWG
Working voltage:	500VAC or DC peak
Contact resistance:	500mΩ
Insulation resistance:	10mΩ
Temperature range:	-55°C to 125°C
Materials:	1. shell: steel with 3-5 u" zinc plating over yellow chromate 2. insulators: polyester 30% glass filled gray 3. contacts: copper alloy, gold plated over nickel
Spacing of rows:	2.84mm (.11)

Mouser Stock No.	Type	# contacts	A	B	C	D	E
152-5209	Plug	9	1.213	.984	.488	.431	.984
152-5309	Recept	9	1.213	.984	.488	.431	.984
152-5215	Plug	15	1.543	1.311	.488	.755	1.311
152-5315	Recept	15	1.543	1.311	.488	.755	1.311
152-5225	Plug	25	2.091	1.850	.488	1.304	1.852
152-5325	Recept	25	2.091	1.850	.488	1.304	1.852
152-5237	Plug	37	2.736	2.500	.488	1.956	2.500
152-5337	Recept	37	2.736	2.500	.488	1.956	2.500
152-5250	Plug	50	2.638	2.406	.606	1.739	2.406
152-5350	Recept	50	2.638	2.406	.606	1.739	2.406

152-5309, 152-5315, 152-5325, 152-5337, 152-5350

D-Sub Connector PC Pins 152-5209, 152-5215, 152-5225, 152-5237, 152-5250

Date Last Revised: 10-17-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300227