



General ordering data

Order No.	1706950000
Part designation	VG EMV M25X1,5
Version	Cable gland, Brass, nickel-plated, External thread: M 25 x 1.5
EAN	4008190917708
Qty.	25 pc(s).

General details

AF size 1	30 mm
Assembly temperature, max.	135 °C
Assembly temperature, min.	-40 °C
Clamping range, max.	18 mm
Clamping range, min.	14 mm
Class of protection with thread gasket	IP 68 - 10 bar
External thread	M 25 x 1.5
Length	43 mm
Length of thread	11 mm
Material	Brass, nickel-plated
O-Ring	Perbunan
Protection class	IP 68
Sealing	CR
Type of cable gland	metric

Approvals

Approvals institutes



Classifications

eClass 4.1	27-14-12-09
eClass 5.0	27-14-91-09
eClass 5.1	27-14-91-09

Classifications

Similar products

Order No.	Part designation	Version
1706920000	VG EMV M18X1,5	Cable gland, Brass, nickel-plated, External thread: M 18 x 1.5
1706940000	VG EMV M20X1,5	Cable gland, Brass, nickel-plated, External thread: M 20 x 1.5
1706930000	VG EMV M24X1,5	Cable gland, Brass, nickel-plated, External thread: M 24 x 1.5
1706870000	VG EMV PG 11	Cable gland, Brass, nickel-plated, External thread: PG 11
1706880000	VG EMV PG 13,5	Cable gland, Brass, nickel-plated, External thread: PG 13.5
1706890000	VG EMV PG 16 K14	Cable gland, Brass, nickel-plated, External thread: PG 16
1713880000	VG EMV PG 16 K18	Cable gland, Brass, nickel-plated, External thread: PG 16
1706900000	VG EMV PG 21 K18	Cable gland, Brass, nickel-plated, External thread: PG 21
1713890000	VG EMV PG K28	Cable gland, Brass, nickel-plated, External thread: PG 21
1706910000	VG EMV PG 29 K26	Cable gland, Brass, nickel-plated, External thread: PG 29
1713900000	VG EMV PG 29 K29	Cable gland, Brass, nickel-plated, External thread: PG 29
1770410000	VG EMV PG36 K32-27	Cable gland, Brass, nickel-plated, External thread: PG 36
1713870000	VG EMV PG 7/9	Cable gland, Brass, nickel-plated, External thread: PG 7
1706860000	VG EMV PG 9/11	Cable gland, Brass, nickel-plated, External thread: PG 9