


Multistage Series MS4,129,10,15

Thermoelectric Modules



The MS Series of thermoelectric modules (TEMs) are designed to reach cool down temperatures that are not achievable with single stage TEMs. This product line is available in numerous heat pumping capacities, geometric shapes and temperature differentials. Assembled with Bismuth Telluride semiconductor material and thermally conductive Aluminum Oxide ceramics, the MS Series is designed for higher current and lower heat-pumping applications.

FEATURES & BENEFITS

- High temperature differential
- Precise temperature control
- Reliable solid state operation
- Environmentally friendly
- DC operation
- RoHS compliant



MARKETS

- CCD cameras
- Electron microscope
- Calibration equipment
- Photonics laser systems
- Gas analyzers
- Infrared (IR) Sensors
- Guidance systems

SPECIFICATIONS

PERFORMANCE SPECIFICATIONS

Hot Side Temperature (°C)	25
Qmax (Watts)	1.9
Delta Tmax (°C)	115
Imax (Amps)	1.8
Vmax (Volts)	8.3

SUFFIX	THICKNESS PRIOR TO TINNING	FLATNESS & PARALLELISM	HOT FACE	COLD FACE	LEAD LENGTH
00	0.500"± 0.016"	0.001" / 0.004"	Metallized	Metallized	7.87"
11	0.492"± 0.008"	0.001" / 0.002"	Lapped	Lapped	7.87"
22	0.500"± 0.016"	0.001" / 0.004"	Metallized	Metallized	7.87"

SEALING OPTION


SUFFIX	SEALANT	COLOR	TEMP RANGE	DESCRIPTIONS
RT	RTV	White	-60 to +204°C	Non-corrosive, silicone adhesive sealant
EP	Epoxy	Black	-55 to +150°C	Low density syntactic foam epoxy encapsulant

Multistage Series MS4,129,10,15



Thermoelectric Modules

Performance curves at $T_h = +25^\circ\text{C}$

THERMO



ELECTRIC



Ceramic material: 100% Alumina ceramics

Solder construction: 138°C Tin Bismuth Tin (BiSn)

OPERATING TIPS

- Max operating temperature: 80°C
- Do not exceed I_{max} or V_{max} when operating module
- Reference assembly guidelines for recommended installation
- Solder tinning also available on metallized ceramics

THR-DS-MS4,129,10,15_0614

Any information furnished by Laird and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird, Laird Technologies, Inc. or any of its affiliates or agents shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2014 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.