

LIGHTS

1900
MityLite

Save as PDF



Peli lights - 1900 Flaslights for industry



Black Yellow Blue Orange White Submersible

Unlike other torches in the market that have a yellowish beam, the MityLite 1900 uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact torch to cut through thick smoke, fog, and dust. It is submersible and comes with a twist on/off lens shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.

Materials

Peli lights - 1900 Flaslights for industry

ANSI FL1 Specifications

FL1 STANDARD		High	
LIGHT SOURCE.	Xenon		
BATTERIES	2 AAA Alkaline (Included)		
CHARGE TIME	N/A		
VOLTAGE	3		
LENGTH	10.4 cm (4.09")		
WEIGHT W/ BATTERIES	0.09 kg (3 oz.)		
WEIGHT W/ O BATTERIES	0.02 kg (0.75 oz.)		

Body	Lens	Shroud	Switch Type
Xenoy Polymer Resin	Polycarbonate Resin	Xenoy Polymer Resin	Twist On/Off Lens Shroud
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
N/A	Phosphore/Bronze	Ethylene Propylene	N/A

Configuration

Cat. #	Description

Peli lights - 1900 Flaslights for industry Accessories

Cat. #	Description

FL1 STANDARD		High	
LIGHT OUTPUT			
RUNTIME (hours/min)		1h 30m	
BEAM DISTANCE (meters)		45m	
PEAK BEAM INTENSITY (candela)		571cd	
WATER RESISTANT			

Approvals

- Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.

- Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X

- Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783