



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company
 portrait
 corporate association
 location maps
 fairs and exhibitions
 jobs
 imprint
 terms and conditions

Home ▶ sockets ▶ sockets ▶ KUN 30

KUN 30

datasheet for KUN 30
article number: 931804104



[View Full-Size Image](#)



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 931 804-104
description:	Shatter-proof, flexible, insulated coupling for a 4 mm diameter plug and solder connection up to a cable cross-section of 2.5 mm ² . Nickel-plated brass socket.
typ:	KUN 30 gruen/green
system:	4mm system
order number:	931 804-104
color	
other color versions:	     
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	unsprung socket Ø 4 mm
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	16 A
Please consider derating curve!	
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	
	